








SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OPEN	2-1





NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = 0.4
X.XX = 0.25
3. TERMINAL NO'S FOR REFERENCE ONLY.
- ▲ 4. CONTACT RATINGS:
ANSI/UL 508 (E195908)
20A 125VAC [cURus]
12A 250VAC [cURus]
5. CONTACT RESISTANCE: 50mΩ MAX.
6. INSULATION RESISTANCE: 5MΩ @ 500VDC
7. DIELECTRIC STRENGTH: 1,500VAC FOR 1 MINUTE
8. ELECTRICAL LIFE: 6,000 CYCLES
9. OPERATING TEMP: 0°C TO 85°C
10. ▲ DENOTE CRITICAL PARAMETER
11. 2002/95/EC (ROHS) COMPLIANT
12. INGRESS PROTECTION: IP54



DETAIL A



TITLE PB241D1A21

A	21492	RELEASE FOR PRODUCTION	6/25/14	EBP
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE 6/25/2014	DR EBP	DWG 34-PB241D1A21	REV A
-------	-------------------	-----------	----------------------	----------