



DESCRIPTION: 979 SERIES D-SUB BACKSHELL - DIE CAST

ALL TOLERANCES = ± 0.3
UNLESS OTHERWISE INDICATED

DESIGNED TO ACCOMMODATE STANDARD:
D-SUB - Shell Size 3

BACKSHELL KIT INCLUDES:

2 - BACKSHELL HALVES
2 - 4-40 MATING SCREWS
2 - SADDLE WASHERS
2 - HOUSING SCREWS
2 - HOUSING NUTS
1 - GROMMET TREE - VARIOUS SIZES
(NON-CONDUCTIVE GROMMETS)



UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OF SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:

04-20-10

SCALE:

NTS

SHEET

1

OF

2

REV

5



DWG. NO.

979-025-030R121


RoHS COMPLIANT

NorComp


DESCRIPTION: 979 SERIES D-SUB BACKSHELL - HARDWARE



HOUSING SCREW



SADDLE WASHER





HOUSING NUT

ALL HARDWARE:


MATERIAL = STEEL
PLATING = NICKEL

RoHS COMPLIANT

MAX. CABLE DIAMETER



MATERIAL: NON CONDUCTIVE PVC - BLACK
P/N: 162-000-925R000



UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OF SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:

04-20-10

SCALE:

NTS

SHEET

2

OF

2

REV

DWG. NO.

979-025-030R121

NorComp