








Mounting Dimensions




Circuit



Technical Data:

Case Material	PA GF black
Switch Lever Material	PA GF black
Min. Insulation Resistance	100MΩ
Dielectric Withstanding Voltage	1050V-1min.
Max. Contact Drop during Resistive Load	150mV
Voltage	up to 32VDC
Duty Rating	300A
Overload	1200A-2min.
	1600A-30sec.
	2000A-3sec.
Sealing	IP 67/ IEC 529
Vibration	4G/ 50-2000Hz
Shock G-Lever	6G/ 11ms
Weight	~420g / 0.93 pound
Temperature Range	-40°C to +85°C
Wire Section (At Nominal Load)	min. 70mm ²
Switch Lever	not removeable
Torque (Main Terminals)	15-20Nm



1:3

For this drawing we reserve the copyright in accordance with DIN ISO 16016

	Date	Name	mm	Scale
Create	20.01.2012	Grind	↔	1:2
Edited	13.07.2020	Seege	General Tolerances DIN ISO 2768 cL	
Check	13.07.2020	Grind		



Drawing No:

35-314-131-S-902

NSN: