

B

A


D10100DB/17

PANDUIT PART #	WIRE RANGE		COLOR (DIN)	WIRE STRIP LENGTH +1/32 -0 [+0,8 -0]	WIRE CLASS	DIMENSIONS in. [mm]				MAX WIRE INSUL DIA	INSTALLATION TOOLS/DIES	
	AWG	[mm ²]				L	P	ID	OD (REF.)		MANUAL	PNEUMATIC
* FSDX75-8	22-20	[0,50]	WHITE	15/32 [11,91]	B, K, M	0.53 [13,5]	0.31 [8,0]	0.04 [1,1]	0.05 [1,4]	0.12 [3,0]	CT-1002 CT-1003 CT-1090 ^CD-090 CT-1123 CT-1160 CT-1170 #CT-2523CH	CTFP-25 CTFP-40
FSDX76-8	18	[0,75]	GRAY	15/32 [11,9]	B, K, M	0.55 [14,0]	0.31 [8,0]	0.05 [1,3]	0.06 [1,6]	0.14 [3,4]		
FSDX77-8	-	[1,0]	RED	15/32 [11,9]	B, K, M	0.57 [14,5]	0.31 [8,0]	0.06 [1,5]	0.07 [1,8]	0.14 [3,4]		
FSDX78-8	16	[1,5]	BLACK	15/32 [11,9]	B, K, M	0.57 [14,5]	0.31 [8,0]	0.07 [1,8]	0.08 [2,1]	0.15 [3,8]		
FSDX78-10				17/32 [13,5]	B, K, M	0.63 [16,0]	0.39 [10,0]					
FSDX80-8	14	[2,5]	BLUE	15/32 [11,9]	B, K, M	0.63 [16,0]	0.31 [8,0]	0.09 [2,3]	0.10 [2,6]	0.19 [4,8]		
FSDX80-12				5/8 [15,9]	B, K, M	0.79 [20,0]	0.47 [12,0]					
FSDX81-10	12	[4,0]	GRAY	17/32 [13,5]	G, K, M	0.71 [18,0]	0.39 [10,0]	0.11 [2,9]	0.13 [3,3]	0.24 [6,2]		CTFP-40 CTFP-100
FSDX81-12				5/8 [15,9]	G, K, M	0.79 [20,0]	0.47 [12,0]					
FSDX84-12	6	[16,0]	BLUE	5/8 [15,9]	G, H, I, K, M	.91 [23,0]	0.47 [12,0]	0.24 [6,0]	0.25 [6,4]	0.37 [9,5]	+CT-1004 CT-1104 #CT-2504CH	---

* UL LISTED WITH 20 AWG ONLY, UL486F SCOPE IS 20 - 1/0 AWG. WHITE IS DIN COLOR FOR 20 AWG [0,5]
+ TOOL/PART IS NOT A UL LISTED COMBINATION
^ DIES USED WITH CT-2300 TOOL
CRIMP HEAD USED WITH CT-2500 TOOL

NOTES:

1. USED FOR:
A. UL LISTED WITH STRANDED COPPER WIRE ONLY
B. 221°F [105°C] MAX. OPERATING TEMPERATURE
2. MATERIAL:
A. STAMPING: COPPER, TIN PLATED
B. HOUSING: POLYPROPYLENE, COLOR CODED
C. COLOR CODE CONFORMS TO DIN STANDARD
3. SEE www.panduit.com FOR PACKAGE QUANTITIES
4. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT




LISTED
E472545



CERTIFIED
LR31212

09	8/18	FCHE	TMR	RGB	ADDED FSDX78-10, FSDX80-8, FSDX80-12, FSDX81-10, FSD81-12 & CTFP SERIES TOOLS	040535
08	3/17	TMR	RGB	RGB	ADDED TOOL INFORMATION RELATED TO CT-2500 TOOL	A41752
07	11/16	JHNU	JLOV	RGB	ADDED CT-1090, CT-2300, CT-1160, CT-1170	A41752
06	8/16	JHNU	JLOV	RGB	ADDED CT-2523CH, CT-2504CH	A41752
05	6/15	JHNU	JHNU	RGB	REVISED STRIP LENGTH FOR PSDX84-12: 5/8 WAS 7/8	A41752
04	6/15	TMR	RGB	VMB	UL LISTED, ADDED WIRE CLASS, MAX WIRE INSUL DIA TO DRWG	A41752
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE FERRULES WITH SLEEVES SINGLE WIRE DIN END SLEEVES FSDX: LARGER SLEEVE DIAMETER CUSTOMER/AGENCY DRAWING					
ITEM REVISION NAME N41752BA/09					
DATASET FILE NAME N41752BA_DC/09					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 ° 				MATERIAL : SEE NOTES	
THIRD ANGLE PROJECTION				DRAWING NUMBER : A41752	
DRAWN BY FCHE	DATE 8/31/2018	CHK	SCALE N.T.S.	SHT 1 OF 1	SIZE B