


P.C.B. LAYOUT

DimA=Nx3.5
DimB=(N-1)x3.5

N=1/2Number of contacts

POLES	TOL
2x2p-2x6p	+0.15/-0.15
2x7p-2x12p	+0.20/-0.20
2x13p-2x18p	+0.25/-0.25
2x19p-2x24p	+0.30/-0.30



SIGN	DATE	DESCRIPTION	APPROVER
△	01/18'07	Soldering temperature changed from 245° to 250°	Tason
△	01/18'07	Part NO is Changed	Tason
△	6/06'08	Voltage rating is Changed 150V to 300V	Marvin
△	6/06'08	Operating temperature is Changed	Marvin

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing : Thermoplastic (UL 94V-0)
- Item 2 Clamp : Brass ,Ni plated
- Item 3 Wire guard solder pin : Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

Electrical cULus

- △ ● Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-24
- Stranded wire(AWG): 16-24
- Torque(Lb-In): 1.7
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- △ ● Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

△ YQ xx 21 x 0 xxxx G

04 2x2 CONTACTS 0 Black 0000:"@Logo (Standard) Pb < 40,000ppm
06 2x3 CONTACTS 5 Green 000A:"ANYTEK"Logo (RoHS)
... ... 6 Blue Any special item by
48 2x24 CONTACTS 8 Grey customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		DWG NO.			Tolerance	
PART NO.		DRAWN		CUST NO.	UNIT: mm	X. ±0.50
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	SCALE: NONE	X.X ±0.30
	Marvin 2008.06.06	Marvin 2008.06.06	Marvin 2008.06.06		Ø1.30	X.XX ±0.10
						X° ±1°
					SHEET: 01/01	REV.: E