

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20


© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REVISED PER ECO-20-002238	7-22-20	CT	PD




REFERENCE: 135148-2

BODY: COPPER ASTM-B187 ANNEALED
TIN PLATED 0.003[.000150] MIN THICK
PER MIL-T-10727

INSERT AND FUNNEL: BRASS ASTM B36
NICKEL PLATED SAE AMS QQ-N-290A
DATED JULY 2000, .00254[.000100] MIN THICK

NOTES:

- 1) WIRE INSULATION: 7.01-7.75 [.276-.305]
- 2) WIRE CMA: 42331
- 3) THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.
- 4) WEIGHT: 21 GRAMS



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. BELACK 16SEP2015	TE Connectivity		
DIMENSIONS: mm [INCH]		CHK P. D'AMATO 16SEP2015			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD P. D'AMATO 16SEP2015	NAME SEALED COPALUM		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC -	-		
MATERIAL -		APPLICATION SPEC -	-		
FINISH -		WEIGHT -	SIZE A3	CAGE CODE -	DRAWING NO C-135148
		Customer Drawing	SCALE 2:1	SHEET 1 OF 1	REV H