




REV. 1 3/23/99

DCO 140960

COIL: @ 25°C

RESISTANCE 50 OHMS $\pm$ 10%

NOMINAL VOLTAGE 5.0 VDC

MUST OPERATE 2.7 VDC

MUST RELEASE 0.22 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX

RELEASE TIME 1.5 MS MAX

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 10/3/97 *[Signature]* 3-23-99

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. C.I.I. STD.

CUST. NO.

TYPE 'MGA' RELAY

MGAC-5