


LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	ECR-06-001518	26JAN06	JMS	FWK


NOTES:

- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Au PLATING
- 4 Ni PLATING
- 5 THIS ITEM MUST BE WHITE

- 6 ELECTRICAL CHARACTERISTICS
FREQUENCY RANGE: DC - 4 GHz
NOMINAL IMPEDANCE: 50 Ohm
INSULATION RESISTANCE: 5000 MOhm
WORKING VOLTAGE: 500 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE: 1500 Volts RMS Max
CONTACT RESISTANCE:
CENTRE CONTACT: 1.50 mOhm Max
OUTER CONTACT: 0.20 mOhm Max
VSWR @ 4GHz: 1.30:1 Max
INSERTION LOSS dB @ x 3 GHz: 0.20 Max
- 7 MECHANICAL CHARACTERISTICS
COUPLING NUT RETENTION FORCE: N/A
CABLE RETENTION FORCE: 170N Min
CLAMP NUT RECOMMENDED TORQUE: 4N
DURABILITY: 500 Cycles Min
- 8 ENVIRONMENTAL CHARACTERISTICS
OPERATING TEMPERATURE: -65 to +165 DegC



RECOMMENDED
CABLE STRIPPING DIM'S



		1	1	BRASS	4	CLAMP NUT	8
		1	1	BRASS	4	WASHER	7
		1	1	BRASS	4	BUSH	6
		1	1	BRASS	4	SLEEVE	5
		1	1	SILICONE RUBBER	5	GASKET	4
		1	1	BRASS	3	CONTACT	3
		1	1	PTFE		INSULATION	2
		1	1	BRASS	4	BODY	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		4	1				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.SANDWELL	26JAN06	tyco Tyco Electronics Corporation Electronics Bideford EX39 4HE		
		CHK	S.PARLOW	26JAN06			
		APVD	F.WHEELER-KING	26JAN06	NAME		
		PRODUCT SPEC			BNC STRAIGHT JACK MIL-CLAMP 50 OHM RG58C/U, 141A/U, URM43, 76, BELDEN 9907, KX15		
		APPLICATION SPEC			-		
		411-3232			SIZE	CAGE CODE	DRAWING NO
		WEIGHT			A3	00779	C-1337536
		CUSTOMER DRAWING			SCALE	SHEET	REV
					NTS	1 OF 1	C