






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	PART STATUS UPDATED	11JAN2018	RK	PS



1776118-4 AS SHOWN

- 1 MATERIAL AND FINISH:
HOUSING: HIGH TEMP POLYAMIDE, UL 94V-0 RATED,
COLOR - BLACK
CLAMP: BRASS, NICKEL PLATED
TERMINAL: BRASS, TIN PLATED
CLAMPING SCREW: M3, BRASS, NICKEL PLATED
- 2 END-TO-END STACKABLE WITHOUT LOSS OF
CENTERLINE SPACING
- 3 WIRE SIZE RANGE: 16-28 AWG
- 4 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE NO. E60677
- 5 IMQ CERTIFICATE WITH SURVEILLANCE IN COMFORMITY
WITH IEC 998-17998-2-1.



RECOMMENDED PC BOARD
LAYOUT

OBSOLETE	TAPE AND REEL	15.0	3	1-1776118-3
	-	40.0	8	1776118-8
	-	35.0	7	1776118-7
	-	30.0	6	1776118-6
	-	25.0	5	1776118-5
	-	20.0	4	1776118-4
	-	15.0	3	1776118-3
	-	10.0	2	1776118-2
PACKAGING		L.	NUMBER OF POSN.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 28OCT2010	TE Connectivity		
		CHK C. RICHARD 28OCT10			
DIMENSIONS: mm		APVD C. RICHARD 28OCT10	NAME TERMINAL BLOCK ASSEMBLY, PCB MOUNT, SIDE ENTRY WIRE, STACKING 5.00mm PITCH		
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE A2		
MATERIAL		WEIGHT	CAGE CODE 00779	DRAWING NO C-1776118	RESTRICTED TO -
FINISH		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1
				REV A2	