



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F4	REVISED PER ECN-22-150900	28APR2022	RK	CSD



AMP WIRE RANGE
2/0 AWG STRANDED

- 1 STAMP AMP 2/0 W*, LOCATE APPROX AS SHOWN.
- 2 BODY MATERIAL THK 2.032±0.051 [.080±.002]
- 3 WIRE INSULATION ø15.494 [ø.610] MAX.
- 4 BODY: COPPER PER ASTM B-152
INSULATION: NYLON ASTM D4066 TYPE I.
- 5 BODY: TIN PLATED PER ASTM B-545
INSULATION: COLOR-YELLOW.

50	LOOSE PC	324084
QTY	PACKAGE TYPE	PART NO

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 9-28-93		TE Connectivity			
			CHK R. HERSEY 9-28-93					
VOLTAGE RATING: —	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.127[.005] 4 PLC ± — ANGLES ± —		APVD M ELLIS 9-28-93	NAME TERMINAL, RING TONGUE, TERMINYL, WIRE SIZE: 2/0 AWG —			
				PRODUCT SPEC —				
CIRCULAR MIL AREA: 60.6–76.3mm ² [119,500–150,500] STRANDED		APPLICATION SPEC —	SIZE	CAGE CODE				
	MATERIAL 	FINISH 	WEIGHT —	A3	00779	C-324084		
	CUSTOMER DRAWING			SCALE	NTS	SHEET	1 OF 1	REV