

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N9	3- -3 AND 3- -4 PARTS ADDED	25NOV2021	SCB	SS

NOTES:

MATERIAL:
HOUSING: THERMOPLASTIC PA, UL94V-0, BLACK.
TERMINAL: BRIGHT TIN PLATED, COPPER ALLOY.
SCREW: 6-32, STEEL, ZINC PLATED CLEAR CHROMATE.

ELECTRICAL:
UL CLASS C: 20A, 150V.
UL CLASS D: 10A, 300V.
CSA TYPE B: 20A, 300V.
CSA TYPE C: 20A, 300V.
CSA TYPE D: 10A, 300V.
CSA TYPE E: 20A, 300V.
WIRE RANGE: 12-22 AWG

MECHANICAL:
MAXIMUM TORQUE RATING: 7 IN-LBS.
RUNNING TORQUE: 0.5-3.5 IN-LBS UNLESS OTHERWISE STATED.


- 1 SCREWS ARE BOTTOMED, NO THREAD INTERRUPT.
- 2 SCREWS ARE NICKEL PLATED BRASS.
- 3 SCREWS ARE CAPTIVE.
- 4 SEE FIGURE.
- 5 PRELIMINARY PART NUMBER.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 7 TERMINAL FINISH: MATTE TIN
- 8 OBSOLETE
- 9 SCREWS ARE IN TIGHTENED CONDITION

9	.160	4DB-P108-05-SPCL	1.690	5	3-796658-4
9	.160	4DB-P108-03-SPCL	1.040	3	3-796658-3
8	.160	4DB-P108-04-SPCL	1.365	4	3-796658-0
8	.160	4DB-P108-03-SPCL	1.040	3	2-796658-9
8	.160	4DB-P108-30	9.815	30	5-1437667-5
8	.160	4DB-P108-29	9.490	29	796658-9
8	.160	4DB-P108-28	9.165	28	5-1437667-3
8	.160	4DB-P108-27	8.840	27	796658-8
8	.160	4DB-P108-26	8.515	26	5-1437667-2
8	.160	4DB-P108-25	8.190	25	796658-7
8	.160	4DB-P108-24	7.865	24	5-1437667-0
8	.160	4DB-P108-23	7.540	23	796658-6
8	.160	4DB-P108-22	7.215	22	4-1437667-8
8	.160	4DB-P108-21	6.890	21	796658-2
8	.160	4DB-P108-20	6.565	20	4-1437667-6
8	.160	4DB-P108-19	6.240	19	4-1437667-5
8	.160	4DB-P108-18	5.915	18	4-1437667-4
8	.160	4DB-P108-17	5.590	17	4-1437667-2
8	.160	4DB-P108-16	5.265	16	4-1437667-0
8	.160	4DB-P108-15	4.940	15	3-1437667-9
2	.160	4DB-P108-14-102	4.615	14	2-796658-5
2	.160	4DB-P108-14-102	4.615	14	2-796658-3
	.160	4DB-P108-14	4.615	14	3-1437667-8
	.160	4DB-P108-13	4.290	13	3-1437667-7
	.160	4DB-P108-12	3.965	12	3-1437667-6
	.160	4DB-P108-11	3.640	11	3-1437667-5
	.160	4DB-P108-10	3.315	10	3-1437667-3
8	.160	4DB-P106-09-094	2.990	9	1-796658-7
	.160	4DB-P108-09	2.990	9	3-1437667-2
6	.160	4DB-P108-08-091	2.665	8	1-796658-4
	.160	4DB-P108-08	2.665	8	3-1437667-1
8	.160	4DB-P106-07-100	2.340	7	2-796658-2
	.160	4DB-P106-07-093	2.340	7	1-796658-6
	.160	4DB-P108-07	2.340	7	3-1437667-0
8	.160	4DB-P106-06-099	2.015	6	2-796658-1
6	.160	4DB-P108-06-090	2.015	6	1-796658-3
8	.200	4DB-P108-06	2.015	6	2-796658-6
	.160	4DB-P108-06	2.015	6	2-1437667-9
8	.160	4DB-P106-05-098	1.690	5	2-796658-0
6	.160	4DB-P108-05-093	1.690	5	1-796658-5
	.160	4DB-P108-05	1.690	5	2-1437667-8
8	.160	4DB-P106-04-097	1.365	4	1-796658-9
	.160	4DB-P108-04-089	1.365	4	1-796658-2
	.160	4DB-P108-04	1.365	4	2-1437667-6
8	.160	4DB-P106-03-096	1.040	3	1-796658-8
6	.160	4DB-P108-03-088	1.040	3	1-796658-1
	.160	4DB-P108-03	1.040	3	2-1437667-5
7	.142	4DB-P108-02-143	.715	2	2-796658-8
	.142	4DB-P108-02-142	.715	2	2-796658-7
	.160	4DB-P108-02	.715	2	2-1437667-4
DIM B		CATALOG NUMBER	DIM A	NO OF POS.	PART NUMBER

2-1437667-4

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S WELDON 01MAY2003		TE Connectivity							
DIMENSIONS: INCHES		CHK S YODER 5/1/03									
		APVD S YODER 5/1/03		NAME ASSEMBLY, DUAL BARRIER 4DB P108 XX —							
		PRODUCT SPEC —									
		APPLICATION SPEC —									
		WEIGHT —									
TOLERANCES UNLESS OTHERWISE SPECIFIED:				SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
0 PLC ± —				A2		00779		C-2-1437667-4		—	
1 PLC ± —				CUSTOMER DRAWING							
2 PLC ± .01											
3 PLC ± .005											
4 PLC ± —											
ANGLES ± 1°				SCALE		NTS		SHEET		1 of 1	
MATERIAL —		FINISH —								REV N9	

