


VER	Description	ECN	Name	Date
A	Initial Released	N/A	Patrick	2018/10/20




I. MATERIALS & FINISHES			
Component	Material	Finishes	Thk. (u")
Body	Brass	Sn-Ni	100
Contact Pin	Beryllium Copper	Gold	50
Insulator	PTFE	--	--
Coupling Nut	Brass	Sn-Ni	100
Ferrule	Copper	Sn-Ni	100
Gasket	Silicone Rubber	--	--

II. ELECTRICAL PROPERTIES	
Impedance (Ω):	50
Frequency Range (GHz):	DC~8 GHz
Dielectric Withstanding Voltage (V r.m.s):	1500
Insulation Resistance (MΩ):	≥5000
VSWR:	≤1.30 (DC~6 GHz)
	≤1.40 (6~8 GHz)
Insertion Loss (dB, f / GHz):	-0.1 x sqrt (f)

III. ENVIRONMENT PROPERTIES	
Temperature Range:	-40℃~+125℃
Thermal Shock:	MIL-STD-202, Meth. 107, Cond. B
Vibration:	MIL-STD-202, Meth. 204, Cond. B
Shock:	MIL-STD-202, Meth. 213, Cond. G
Climatic Class:	IEC 60068 55/155/21
RoHS:	Compliant

IV. MECHANICAL PROPERTIES	
Center Conductor:	Spring Finger
Outer Conductor:	Crimp
Coupling Nut Torque (in-lbs):	4.1~6.1
Cable-Connector Retention Force (lbs):	180
Durability (Cycles):	500

V. Tooling & Accessories
Stripping Tool: 3192-075/CST-500
Crimping Tool: 3192-169/CT-500
Heat Shrink Tube: 1"x2" (3:1) 1 pcs



RECOMMENDED CABLE STRIPPING DIM'S
Connector Adds: 22.4 mm

Compatible with Standard: IEC 60169-17

UNLESS OTHERWISE SPECIFIED						DFTM Patrick		 EZ-500-TM-RA-X TNC Male (Plug) Right Angle Non-Solder Pin No Braid Trim Connector for LMR-500 Cable		
ALL DIMENSIONS ARE IN mm MACHINED SURFACES FINISH 1.6 RMS MAX. REMOVE ALL BURRS 0.15X45° MAX. BREAK MACHINE CORNERS 0.15X45° D MAX. FILLET R. TOLERANCES ON DECIMALS .X ±0.1 .XX ±0.15 ANGLES ±2° FRACTIONS ±N/A						DATE	2018/10/20			
						CHKD	Monica			
						DATE	2018/10/20			
						APPD	Joslen	3190-8030		
						Scale:	3:1			
Size:		A3	CODE IDENT	68999	DATE	2018/10/20	SHT	1/1	REV	A