

Bandpass Filter

50Ω 404 to 426 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W at 25°C
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

RF IN	2
RF OUT	6
GROUND	1,3,4,5,7,8

Outline Drawing





Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
.350	.350	.100	.175	.075	.100	.110	.040	.080
8.89	8.89	2.54	4.45	1.91	2.54	2.79	1.02	2.03
K	L	M	N	P	Q	R	wt	
.050	.040	.195	.390	.120	.390	.070		
1.27	1.02	4.95	9.91	3.05	9.91	1.78		

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-332 Suggested PCB Layout (PL-176)



Features

- linear phase, up to ±7deg typ. @ Fc ±45MHz
- good VSWR, 1.2:1 typ. @ passband
- small size 0.35" x 0.35"
- shielded case
- aqueous washable


Applications

- harmonic rejection
- transmitters / receivers
- CDMA


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 3dB)	STOPBANDS (MHz)				MAXIMUM DEVIATION FROM LINEAR PHASE (deg.) Fc ± 45MHz	VSWR (:1)	
		Loss > 20dB		Loss > 35dB			Passband	Stopband
		F3	F4	F5	F6		Max.	Typ.
Fc	F1 - F2	F3	F4	F5	F6			
415	404 - 426	225	550	120	750-2000	±10	1.7	18

Typical Frequency Response




Functional Schematic




Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Deviation from Linear Phase (deg)
0.3	99.29	289.53	370.0	0.95
50.0	61.00	193.02	374.0	0.13
120.0	45.73	108.58	380.0	-0.56
225.0	31.41	59.91	386.0	-0.85
318.0	15.95	13.81	390.0	-0.78
328.0	7.41	5.85	396.0	-0.53
340.0	3.23	2.65	404.0	0.06
404.0	1.26	1.27	410.0	0.55
425.0	1.28	1.13	415.0	1.01
426.0	1.28	1.13	422.0	1.45
475.0	3.35	2.24	426.0	1.49
490.0	7.48	5.59	436.0	1.41
510.0	15.50	13.92	440.0	0.99
550.0	32.64	29.96	446.0	-0.11
750.0	49.35	53.46	450.0	-1.32
900.0	66.98	57.91	456.0	-4.22
2000.0	47.47	33.42	460.0	-7.04

RBP-415+ VSWR



RBP-415+ INSERTION PHASE & DEVIATION FROM LINEAR PHASE



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Generic photo used for illustration purposes only

CASE STYLE: GP731

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Reel Size	Available Tape and Reel at no extra cost
7"	10, 20, 50, 100, 200
13"	500, 1000