









REAR VIEW
TERMINAL ARRANGEMENT




RECOMMENDED
PANEL CUT-OUT



CUSTOMER DRAWING

NOTES:

- SWITCH SPECIFICATIONS:
RECTANGULAR ROCKER SWITCH, UL RECOGNIZED
BLACK WITH WHITE "I/O" MARKINGS
CIRCUIT: DPDT
CIRCUIT FUNCTION: ON-ON
RATING: 16A @ 125-250 VAC, 105° C per UL1054
CONTACT RESISTANCE: 0.01Ω MAX. AT 10mA (INITIAL)
INSULATION RESISTANCE: 10⁹MΩ MIN.
DIELECTRIC WITHSTANDING VOLTAGE: 2,500 V FOR 1 MINUTE
ELECTRICAL LIFE: 100,000 CYCLES, NO LOAD, MINIMUM
TERMINAL STYLE: 0.187" [4.75] QUICK CONNECT TABS, SILVER PLATED
- MATERIAL:
FLANGE - ZINC, SEE TABLE FOR FINISH
SWITCH HOUSING AND KNOB - THERMOPLASTIC
SWITCH TERMINALS & CONTACTS - COPPER ALLOY, AND/OR
COPPER ALLOY SILVER PLATED
- FOR FLANGE MOUNTING SCREWS TO BE SHIPPED WITH ASSEMBLY,
ADD THE SUFFIX "PKG" TO THE PART NUMBER.
- THESE PRODUCTS ARE RoHS COMPLIANT.



PART NUMBER	FLANGE FINISH
EHRRSL	NICKEL
EHRRSLB	BLACK

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.02 - THREE PLACE DECIMALS ±0.005	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.													
						SIZE	WIDTH		MULT		LBS/M		TEMPER						
						FINISH SPEC No.						MATERIAL SPEC No.							
						FIRST USED ON *				SCALE 2:1		Switchcraft®							
						DATE DRAWN	BY	CHKD		APVD									
						07/28/09	BS	PNK 01/31/11		SRC 01/31/11									
A	26781	6-9-11	TO	TJK		SHEET 1 OF 1													
REV	ECO NUMBER	DATE	BY	APVD		NAME						PART No.						REV	
						EH SERIES DPDT RECTANGULAR ROCKER SWITCH, RoHS						EHRRL SERIES						A	