

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		B	REV PER ECR-10-007996	19APRIL2010	RG	TM

D

C

B

A




AMP WIRE RANGE	 E13288 Listed
16-14 AWG STRANDED	16-14 AWG STRANDED

- 1 STAMP AMP 16-1, APPROX. AS SHOWN
- 2. RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
- 3. WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180 CIRCULAR MIL AREA] STRANDED
- 4 MATERIAL: COPPER PER ASTM B-152 ANNEALED
- 5 FINISH: TIN PLATE 0.00254 [.000100] MIN THK PER ASTM-B545

33437

B

A

				1000		LOOSE PIECE		33437			
				QTY		PACKAGE TYPE		PART NO.			
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN 19APR2010 R.GRZYBOWSKI		 Tyco Electronics Corporation Harrisburg, PA 17105-3608					
				CHK 19APRIL2010 T.MICHIELUTI							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 19APRIL2010 M.PERCHERKE		NAME TERMINAL, HOOK TONGUE BUDGET —					
mm				PRODUCT SPEC —							
		0 PLC ± —		APPLICATION SPEC —		SIZE A2					
		1 PLC ± —		—							
		2 PLC ± —		—		CAGE CODE 00779					
		3 PLC ± —		—							
		4 PLC ± —		—							
		ANGLES ± —		—							
MATERIAL		FINISH		WEIGHT —		DRAWING NO C-33437					
				CUSTOMER DRAWING		RESTRICTED TO —					
						SCALE 1:1		SHEET 1 of 1		REV B	