








- 1
- CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1.27 CENTERS.
FOR CABLE REQUIREMENTS SEE TE APPLICATION SPECIFICATION 114-19022.
- 2
- THESE RECEPTACLE CONNECTORS MATE WITH 0.64±0.05mm SQUARE OR ROUND POSTS ON 2.54mm GRID.
- 3
- MARK INDICATING FIRST CABLE POSITION REFERRING TO CONTACT POSITION.
- 4
- THERE IS NO POLARIZATION-SLOT AT THIS END IN 6, 10 AND 14 POS CONNECTORS.
- 5
- THESE CONNECTORS CAN BE USED IN CONJUNCTION WITH STRAIN-RELIEF COVERS OF PARTNR: 100103.
- 6
- THERE IS NO POLARIZATION-SLOT AT THIS END IN 6 POS CONNECTORS.
- 7
- PRODUCT SPECIFICATION 108-19033.

③ RECEPTACLE CONTACT	PHOSPHORBRONZE Cu Sn6	AT CONTACT-PLACE: 0,8μ GOLD AT WIRING END: 2,5μ TIN ENTIRE UNDERCOATING:1,27μ NICKEL
② COVER	THERMOPLASTIC POLYESTER GF UL 94 -V0	GREY RAL 7032 ONLY FOR REF.
① HOUSING		
COMPONENT NAME	MATERIAL	PLATING / COLOUR

	500	85,9	64	32	6-215915-4	D
	500	80,8	60	30	6-215915-0	D
	500	68,1	50	25	5-215915-0	D
OBSOLETE	1500	60,5	44	22	4-215915-4	D
	750	55,4	40	20	4-215915-0	D
	1500	47,8	34	17	3-215915-4	D
OBSOLETE	1500	42,7	30	15	3-215915-0	D
	1500	37,6	26	13	2-215915-6	D
	1500	30,0	20	10	2-215915-0	D
	1500	24,9	16	8	1-215915-6	D
	1500	22,4	14	7	1-215915-4	D
	1500	17,3	10	5	1-215915-0	D
	1500	14,8	8	4	0-215915-8	B
	1500	12,2	6	3	0-215915-6	D
OBSOLETE	1500	9,7	4	2	0-215915-4	B
	QUANTITY PER REEL	DIM."C"	"B" CABLE POS.	"A" DUAL POS.	PARTNUMBER ④	PART REV.

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONS: mm
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -
MATERIAL -

DWN 02-02-88 R.HOGEVEEN
CHK 03-02-88 R.VERSTIJNEN
APVD 03-02-88 L.V.SOEST
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -
CUSTOMER DRAWING

TE Connectivity
AMP-LATCH MIL-TYPE RECEPT.
CONN. ASS'Y 14,9 PRE-ASSEMBLED
0.8μm SELECTIVE GOLDPLATE ④
SIZE A2 CAGE CODE 00779 DRAWING NO C-215915
SCALE 5:1 SHEET 1 OF 1 REV E