


SPECIFICATION

Part No. : **MA600.A.ABC.007**

Product Name : MA600 Spartan Screw mount
3in1 Combination Antenna

Feature : GPS/GLONASS/GALILEO 1575~1602MHz
Cellular – GSM/CDMA/HSPA/UMTS
Dual band Wi-Fi 2.4GHz / 5.8GHz
High performance outdoor antenna
Custom cables and connectors available
RoHS Compliant ✓



1. Introduction

The Spartan MA.600 antenna is a heavy-duty, fully IP67 waterproof external M2M antenna for use in telematics, transportation and remote monitoring applications.

The Spartan is unique in the market because it combines a 3in1 GPS/GLONASS/GALILEO, Cellular (2G and 3G) and Wi-Fi, heavy-duty antenna with high efficiency in a compact format. The antenna screws down permanently onto a roof or metal panel and can be pole or wall-mounted with a metal bracket.

For industries such as commercial vehicle telematics, remote monitoring, smart meter systems and construction equipment, the Spartan provides a robust, rugged antenna that is durable, even in extreme environments.

All while still maintaining 20dB isolation between antennas. It uses high-shielded PTFE dielectric ultra low-loss cables that maintain low attenuation at all frequency bands, with an average 0.3dB per meter (0.1dB per foot), compared to 0.7dB for RG58 and 1.2dB for RG174. Because of this, the Spartan maximizes chances of passing PTCRB and network approvals first time. The Spartan also has excellent GPS/GLONASS/GALILEO reception without need to attach to an external ground-plane due to coupling to its unique own metal base.

Note: for ground-isolation antennas use the MA.605 version with Isolation Gaskets.

2. Specification

GPS/GLONASS/GALILEO						
Centre Frequency	1575.42MHz / 1602MHz					
Bandwidth	10MHz					
Radiation Efficiency	50(without cable)					
Passive Gain @ Zenith	4.0 typ(with ψ=140mm ground)					
VSWR	2					
Impedance	50Ω					
DC Power Input Range	3 ~ 5V					
DC input	3.3V		4.0V		5.5V	
MHz	1575.42	1602	1575.42	1602	1575.42	1602
VSWR	2	2	2	2	2	2
LNA Gain	29.2	29	31	31	32.3	32
Noise Figure	3.1	3.1	3.2	3.2	3.4	3.4
Power Consumption	7.5	7.5	9.4	9.4	15	15
Band Attenuation	1520MHz: -20dB 1642MHz: -20dB		1520MHz: -20dB 1642MHz: -20dB		1520MHz: -20dB 1642MHz: -20dB	
Cable	3m RG-174 standard, fully customizable					
Connector	SMA(M) standard, fully customizable					

CELLULAR					
Frequency (GHz)	824~896	880~960	1710~1880	1850~1990	1710~2170
Peak Gain (dBi)	2.1	-0.2	2.9	3.0	5.1
Average (dBi)	-4.7	-7.5	-2.7	-3.1	-3.1
Efficiency	35%	20%	51%	49%	49%
Impedance	50 Ω				
Polarization	Linear				
Radiation Pattern	Omni				
Cable	3m CFD200 standard, fully customizable				
Connector	SMA(M) standard, fully customizable				


WIFI				
Frequency (GHz)	2.4~2.5	4.7~5.0	5.0~5.4	5.4~5.9
Peak Gain (dBi)	2.1	2.9	3.8	2.8
Average Gain (dBi)	-2.3	-3.6	-3.3	-3.8
Efficiency	60%	44%	46%	42%
VSWR	<=1.6:1			
Impedance	50Ω			
Polarization	Linear			
Radiation Pattern	Omnidirectional			
Cable	3m CFD200 standard, fully customizable			
Connector	RP-SMA(M) standard, standard, fully customizable			
MECHANICAL				
Dimensions	Profile 39.5mm x Diameter 145.6mm			
Casing	Wonderloy PC-540 PC/ABS Alloy			
Base and thread	Nickel Plated Zinc			
Thread diameter	30mm			
Waterproof	IP67			
ENVIRONMENTAL				
Temperature Range	-40°C to 85°C			
Humidity	Non-condensing 65°C 95% RH			

* All measurements are done in free space with standard cables


3. GPS/GLONASS/GALILEO Antenna

Characteristics


3.1. Block diagram




3.2. Return Loss



3.3. GPS/GLONASS/GALILEO Antenna Radiation Pattern




MA.600 tested in CTIA approved 3D chamber




XYZ co-ordinate for reference.

3.4. Radiation Pattern


XZ Plane Free Space @1575.42MHz




YZ Plane Free Space @1575.42MHz





XZ Plane Free Space @1602MHz



YZ Plane Free Space @1602MHz




3.5. GPS/GLONASS/GALILEO LNA




4. Cellular Antenna Characteristics


4.1. Return Loss




4.2. VSWR




4.3. Cellular Antenna Efficiency



4.4. Cellular Antenna Peak Gain




4.5. Cellular Antenna 3D Average Gain




5. Cellular Antenna Radiation Pattern

5.1. XY Plane




5.2. XZ Plane




6. 2.4/5.8GHz Antenna Characteristics



6.1. S11 Return Loss





6.2. VSWR





6.3. 2.4/5.8GHz Antenna Efficiency



6.4. 2.4/5.8GHz Antenna Peak Gain




6.5. 2.4/5.8GHz Antenna Peak Gain




7. 2.4/5.8GHz Antenna Radiation Pattern


7.1. XY Plane





7.2. XZ-plane



8. Mechanical Drawing (Unit: mm)



1PCS/BOX




Name	P/N	Material	Finish	QTY
1 Housing	000111F000015A	PC540	Black	1
2 Closed Cell Foam	001011F030001A	CR4305	Black	1
3 3M Double Adhesive	001011F030001A	3M 9448 HK	White Liner	1
4 M30 Nut	000411F000015A	Steel AISI 1006	Ni Plated	1
5 Washer	000411F010015A	Steel AISI 1006	Ni Plated	1
6 M30x 2 Thread 32L	000311F000015A	Zinc Alloy	Ni Plated	1
7 Waterproof Rubber	000711F000015A	Silicone	Black	1
8 GPS-Glass Label	001012K010015A	PEPA	Orange	1
9 2.4/5.8 GHz Label	001016G070000A	PEPA	Teal Green	1
10 Cellular Label	001013B010015A	PEPA	Blue	1
11 Heat Shrink Tube	001315C020000A	PE(RG-174)	Black	1
12 Heat Shrink Tube	001315C030000A	PE(CF200)	Black	2
13 Rubber Stopper	000711F010015A	Silicone Rubber	Black	1
14 Barcode Label	001013G000015A	PEPA	White	1


Name	P/N	Spec	Finish	QTY
W Cable Type	301315C000000A	RG-174	Black	1
WW Cable Type	301415C010000A	CFD-200	Black	2
XX Connector Type	200212G000015A	SMA(M)ST	Au Plated	1
YY Connector Type	200212F000015A	SMA(M)RP ST	Au Plated	1
ZZ Connector Type	200212G010015A	SMA(M)ST	Au Plated	1

NOTES:
1.Part Number : MA.600.A301111.B305111.C305151



9. Installation




Recommended Torque for Mounting 49 N·m
Maximum Torque for Mounting 58.8 N·m



10. Packaging



8 boxes per carton



Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.