




REV. 0

DCO 143325

COIL: @ 25°C

RESISTANCE 390 OHMS ±10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 8.0 VDC

MUST RELEASE 5.2 VDC MAX, 1.1 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX

RELEASE TIME 4.0 MS MAX

CONTACT STABILIZATION 2.5 MS MAX.

# CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 11/26/01

CK [Signature] 11/26/01

**CII Technologies**  
advanced control electronic solutions

CUST. OPL

CUST. NO. M39016/19-028M REV.

"JMGADD" RELAY

JMGAPDD-12M