





Amphenol
FCI

© 2016 APCI


PRELIMINARY

spec ref		-		dr		Andy Lu		2016-10-08		projection		MM		size		A2		scale		4:1			
tolerance std		-		eng		Andy Lu		2016-11-15						ecn no		-							
ASME Y14.5		TOLERANCES UNLESS OTHERWISE SPECIFIED		chr		Terris Liu		2016-11-15						product family		rel level							
surface		linear		0.X		±0.5		Amphenol FCI		title		eHPCE STRADDLE MOUNT		dwg no		10141334		rev		2			
				0.XX		±0.25																2UP6MP2UP+20S	
ASME Y14.5		angular		0°		±2°																cat. no.	






RECOMMENDED HOST BOARD LAYOUT
TOLERANCE ± 0.05

RECOMMENDED HOST BOARD LAYOUT
AS VIEWED



spec ref		-		dr	Andy Lu	2016-10-08	projection		MM	size	A2	scale	4:1	
tolerance std		-		eng	Andy Lu	2016-11-15					ecn no		-	
ASME Y14.5		TOLERANCES UNLESS OTHERWISE SPECIFIED		chr	Terris Liu	2016-11-15	product family		rel level					
appr		PM Zheng				2016-11-15								
surface	linear	0.X	±0.5	Amphenol FCI	title	eHPCE STRADDLE MOUNT				dwg no	10141334		rev	2
		0.XX	±0.25											
		0.XXX	±0.13			2UP6MP2UP+20S								
ASME Y14.5	angular	0°	±2°	cat. no.		Product - Customer Drw				sheet 2 of 4				



RECOMMENDED CARD LAYOUT
TOLERANCE ± 0.05

spec ref		-		dr		Andy Lu		2016-10-08		projection		MM		size		A2		scale		4:1	
tolerance std		-		eng		Andy Lu		2016-11-15						ecn no		-		rel level		-	
ASME Y14.5		TOLERANCES UNLESS OTHERWISE SPECIFIED		chr		Terris Liu		2016-11-15													
				appr		PM Zheng		2016-11-15		product family											
surface		linear		0.X		±0.5		Amphenol FCI		title		eHPCE STRADDLE MOUNT		dwg no		10141334		rev		2	
				0.XX		±0.25															
				0.XXX		±0.13															
ASME Y14.5		angular		0°		±2°				cat. no.		Product - Customer Drw				sheet 3 of 4					

Amphenol FCI