


390-010 Submersible EMI/RFI Cable Sealing Backshell with Strain Relief Type C - Direct Coupling - Low Profile

CONNECTOR DESIGNATORS A-B*-C-D-E-F G-H-J-K-L-S





* Conn. Design. B See Note 6
DIRECT COUPLING

TYPE C OVERALL SHIELD TERMINATION



Length $\pm .060$ (1.52)
Min. Order Length 2.0 Inch
(See Note 4)




STYLE 2
(STRAIGHT
See Note 1)



STYLE C
Medium Duty
(Table X)



STYLE E
Medium Duty
(Table XI)



390-010
Submersible EMI/RFI Cable Sealing Backshell
 with Strain Relief
 Type C - Direct Coupling - Low Profile



See inside back cover fold-out or pages 13 and 14 for Tables I and II.

TABLE III: FRONT ADAPTER			
Shell Size	J Max - Conn. Designator		
	A-E-F	D-B-G-K	C
	J-H-L-S		
08/09	1.180 (30.0)	1.440 (36.6)	
10/11	1.180 (30.0)	1.440 (36.6)	
12/13	1.180 (30.0)	1.440 (36.6)	1.735 (44.1)
14/15	1.180 (30.0)	1.440 (36.6)	1.915 (48.6)
16/17	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)
18/19	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)
20/21	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)
22/23	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)
24/25	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)
28/29	1.610 (40.9)	1.560 (39.6)	1.915 (48.6)
32/33	1.610 (40.9)	1.750 (44.5)	1.915 (48.6)
36	1.610 (40.9)	1.750 (44.5)	1.915 (48.6)
40	1.610 (40.9)	2.190 (55.6)	1.915 (48.6)

TABLE IV: ELBOW DIMENSIONS								
Elbow Size	E Max		F Max		G Max		H Max	
04	.630	(16.0)	2.715	(69.0)	.636	(16.2)	2.725	(69.2)
06	.630	(16.0)	2.775	(70.5)	.710	(18.0)	2.845	(72.3)
08	.692	(17.6)	2.835	(72.0)	.731	(18.6)	2.865	(72.8)
10	.755	(19.2)	3.554	(90.3)	.825	(21.0)	3.564	(90.5)
12	.848	(21.5)	3.664	(93.1)	.988	(25.1)	3.654	(92.8)
16	1.036	(26.3)	3.854	(97.9)	1.087	(27.6)	3.824	(97.1)
20	1.130	(28.7)	4.192	(106.5)	1.325	(33.7)	4.122	(104.7)
24	1.255	(31.9)	4.225	(107.3)	1.337	(34.0)	4.275	(108.6)
28	1.317	(33.5)	4.325	(109.9)	1.827	(46.4)	4.525	(114.9)
32	1.348	(34.2)	4.465	(113.4)	2.027	(51.5)	4.575	(116.2)

TABLE X: CABLE ENTRY							
Dash No.	T Max	W Max	X Ref	Cable Range		Min	Max
03	1.219 (31.0)	.812 (20.6)	.135 (3.4)	.156	(4.0)	.219	(5.6)
04	1.219 (31.0)	.937 (23.8)	.203 (5.2)	.188	(4.8)	.312	(7.9)
06	1.219 (31.0)	1.062 (27.0)	.285 (7.2)	.281	(7.1)	.438	(11.1)
08	1.219 (31.0)	1.188 (30.2)	.350 (8.9)	.312	(7.9)	.531	(13.5)
10	1.281 (32.5)	1.312 (33.3)	.390 (9.9)	.375	(9.5)	.625	(15.9)
12	1.281 (32.5)	1.562 (39.7)	.460 (11.7)	.500	(12.7)	.750	(19.1)
16	1.406 (35.7)	1.750 (44.5)	.510 (13.0)	.625	(15.9)	.938	(23.8)
20	1.656 (42.1)	2.250 (57.2)	.695 (17.7)	.938	(23.8)	1.250	(31.8)
24	1.906 (48.4)	2.375 (60.3)	.715 (18.2)	1.000	(25.4)	1.375	(34.9)
28	1.906 (48.4)	2.625 (66.7)	.915 (23.2)	1.250	(31.8)	1.625	(41.3)
32	2.000 (50.8)	2.812 (71.4)	1.070 (27.2)	1.500	(38.1)	1.875	(47.6)

TABLE XI: CABLE ENTRY							
Dash No.	Y Max	Z Max	Cable Range		Min	Max	
03	.739 (18.8)	.812 (20.6)	.156	(4.0)	.219	(5.6)	
04	.739 (18.8)	.937 (23.8)	.188	(4.8)	.312	(7.9)	
06	.739 (18.8)	1.062 (27.0)	.281	(7.1)	.438	(11.1)	
08	.739 (18.8)	1.188 (30.2)	.312	(7.9)	.531	(13.5)	
10	.791 (20.1)	1.312 (33.3)	.375	(9.5)	.625	(15.9)	
12	.880 (22.4)	1.562 (39.7)	.500	(12.7)	.750	(19.1)	
16	.901 (22.9)	1.750 (44.5)	.625	(15.9)	.938	(23.8)	
20	1.031 (26.2)	2.250 (57.2)	.938	(23.8)	1.250	(31.8)	
24	1.250 (31.8)	2.375 (60.3)	1.000	(25.4)	1.375	(34.9)	
28	1.250 (31.8)	2.625 (66.7)	1.250	(31.8)	1.625	(41.3)	
32	1.312 (33.3)	2.812 (71.4)	1.500	(38.1)	1.875	(47.6)	

1. When maximum cable entry (page 22) is exceeded, Style 2 will be supplied. (Function S only).
2. Metric dimensions (mm) are indicated in parentheses.
3. Cable range is defined as the accommodations range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
4. Consult factory for shorter lengths on straight backshells.
5. Saddles are bottomed on Clamp Ears.
6. When using Connector Designator B refer to pages 18 and 19 for part number development.