

SIGN	DATE	DESCRIPTION	APPROVER
△	07/09'13	update the drawing	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Materials

- Item a Terminal housing : Thermoplastic (UL94V-0)
- Item b Terminal screw : Steel Zinc plating "--" slot type
- Item c Wire guard solder pin 1 : Brass ,Tin plated
- Item d Wire guard solder pin 2 : Brass ,Tin plated
- Item e Wire guard solder pin 3 : Brass ,Tin plated
- Item f Wire guard solder pin 4 : Brass ,Tin plated
- Item g Clamp : Brass, Ni Plated

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-30
- Stranded wire(AWG): 12-30
- Torque(Lb-In): 5.0
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: △

E6 04 0 1 x 1 xxxx G

G RoHS compliant
(lead<4%)
In copper Alloy

COLOR






- | | |
|---------------------|---------------------------------------|
| 0 Black (RAL9005) | 0000: "@" Logo (Standard) |
| 2 Red (RAL3001/D) | 000A: "ANYTEK" Mark |
| 3 Orange(RAL2011/P) | Any special item by customer request. |
| 4 Yellow(RAL1018/A) | please contact sales department. |
| 5 Green(RAL6018/T) | |
| 6 Blue (RAL5015/A) | |
| 8 Grey(RAL7035/D) | |
| 9 White(RAL1102) | |
| C Green(RAL6018/U) | |

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		E6 5.0 SERIES 4P (Left)--Brass				
PART NO.	E60401x1xxxxG			DWG NO.	8E60018	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Guoxue 2013.07.19	Guoxue 2013.07.19		UNIT: mm	X. ±0.5
					SCALE: NONE	X.X ±0.3
					REV.: C	X.XX ±0.1
				SHEET: 01/01	X° ±1°	



P.C.B Layout

