



DIMENSIONS IN M.M. --DO NOT SCALE PRINT

NUMBER
C-160597-E

P	LTR REV	REVISION RECORD MODIFICATIONS	DATE	DWN DESS	APVD VER
	D1	REVISED PER ECO-09-026346	25NOV09	KK	AEG



3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



3 OBSOLETE

ORDER NO.	FINISH	REMARKS
160597-1	NONE	1
160597-3	SILVER- "	1
160597-4	TIN-PLATED	2
160597-5	GOLD-PLATED	1

- 1 FOR USE ON STANDARD APPLICATIONS
(RIGHT-LEFT FEED)
- 2 FOR USE ON MINIATURE APPLICATIONS
(LEFT-RIGHT FEED) AMP-O-MATOR APPLICATION

CUSTOMER PRINT
FOR REFERENCE ONLY

© 1966 BY AMP HOLLAND NV. ALL
RIGHTS RESERVED AMP PRODUCTS
COVERED BY PATENTS AND/OR PAT-
ENTS PENDING

-9	-8	-7	-6	-5	-4	-3	-2	-1	DWG SIZE	NUMBER	NAME	REMARKS	ITEM NO.
REQUIRED PER ASSEMBLY									MATERIAL	HEAT TREAT	FINISH		
									BRASS		SEE TABLE		
									AMP	DR. H/ISSER. 2-22-66	DATE APP. 4-7-66	DATE MODEL 9/16-66	
									AMP-HOLLAND N.V. 1-HERTOGENBOSCH HOLLAND	CHK	DATE APP. 9/16-66	DATE FIRST USED	
									TYPE	PRINT DIST	LOC	SIZE NUMBER	
									A.M.		H A	C-160597-E	
									SCALE	WIRE SIZE	CMA	NAME	
									4-1	0.05-0.15 mm	MAX MIN	"110 BER" PASTON RECEPTACLE	
DESCRIPTION												REV	
												D1	