








RECOMMENDED PCB LAYOUT

TOLERANCE: ± 0.05 (TOP VIEW)










DETAIL F (SCEALE 2:1)

NOTE:

1. MATERIAL:
HOUSING: PA46, WITH 30% GF,
UL 94V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHELL: BRASS.
2. FINISH:
CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA,
GOLD FLASH ON SOLDER TAIL,
WITH ENTIRE CONTACT UNDERPLATED
1.27 μ m [50 μ "] MIN. NICKEL.
SHELL: 0.508 μ m [20 μ "] MIN. NICKEL PLATED.
3. RECOMMENDED PCB THICKNESS: 1.6mm.
4. WAVE SOLDER CAPABLE TO 265°C PER TE SPE
109-202, CONDITION B.

OBSOLETE	1.27μm [50μ"]	2041086-4
	0.762μm [30μ"]	2041086-3
	0.381μm [15μ"]	2041086-2
	0.152μm [6μ"]	2041086-1
	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HSING 12JAN2009 CHK S. CHIEN 12JAN2009 APVD W. KODAMA 12JAN2009		 TE Connectivity	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.30 2 PLC ± 0.20 3 PLC ± 0.15 4 PLC ± - ANGLES ± 3°		NAME MODULAR JACK, RJ11 SINGLE, DIP TYPE	
		PRODUCT SPEC 108-57743		SIZE 5.1 GRAMS	
MATERIAL SEE NOTE		FINISH SEE NOTE		CAGE CODE A300779	
		WEIGHT 5.1 GRAMS		DRAWING NO C-2041086	
		CUSTOMER DRAWING		SCALE = SHEET 1 OF 2 REV B	



13.5 Kg	11.5 Kg	90	25	2250 PCS
GROSS WEIGHT (Ref.)	NET WEIGHT (Ref.)	PCS/TRAY	TRAYS /BOX	QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

MODULAR JACK, RJ11 SINGLE, DIP TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2041086

SCALE

SHEET 2 OF 2

REV B