




Terminals & Splices > Automotive Terminals > MULTILOCK, RECEPTACLE AND TAB



Terminal Type: **Tab**
Mating Tab Width: 1 mm [.039 in]
Mating Tab Thickness: .64 mm [.025 in]
Terminal Transmits: 0 – 24 A (Low Power)
Wire Size: 22 – 20 AWG

[All MULTILOCK, RECEPTACLE AND TAB \(110\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body

Contact Features

Contact Size	1mm
Contact Fabrication	Stamped & Formed
Crimp Type	F-Crimp
Terminal Type	Tab
Mating Tab Width	1 mm[.039 in]
Mating Tab Thickness	.64 mm[.025 in]
Interface Plating	Gold (Au)

Termination Features

--	--



Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Wire Size	.34 – .56 mm²
Wire Size Search	20 AWG, 21 AWG, 22 AWG

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2836994-1 OCEAN_2.0_APPLICATOR-S-FM-067F062F-RSM	 TE Part # 2836994-2 OCEAN_2.0_APPLICATOR-S-FM-067F062FA	 TE Part # 5-2836994-1 OCEAN_2.0_APPLICATOR-S-FM-067F062F-RSM	 TE Part # 5-2836994-2 OCEAN_2.0_APPLICATOR-S-FM-067F062FA
 TE Part # 7-2836974-7 OC-067F062F-752-CRIMPTOOLINGKIT	 TE Part # 7-2836994-7 OCEAN_2.0_SPARE_PART_KIT-067F062F	 TE Part # 7-2836994-1 OCEAN_2.0_APPLICATOR-S-FM-067F062F	 TE Part # 7-2836994-2 OCEAN_2.0_APPLICATOR-S-FM-067F062FA

Also in the Series | Multilock Connector System

 Automotive Connector Caps & Covers (10)	 Automotive Connector Locks & Position Assurance(3)	 Automotive Housings(455)	 Automotive Terminals(115)
 Connector Seals & Cavity Plugs(2)	 Insertion & Extraction Tools(6)	 Other Automotive Connector Accessories(12)	 PCB Headers & Receptacles(152)

Customers Also Bought



TE Part #170454-2
PL 250 AM REC 18-14 0.40 X 21 PRE-TPBR

TE Part #1318801-1
TH/.025 CONNECTOR SYSTEM, HOUSING

TE Part #316833-2
040 SEALED REC CONT S FORMING

TE Part #1612121-1
SQUIB 2POS PLUG HSG

TE Part #1612123-1
SQUIB FERRITE

TE Part #1612124-8
1DIA SOCKET AU

TE Part #2367826-3
84POS,0.5 SERIES,REC HSG ASSY,SLD

TE Part #2367834-1
REC CONN CVR ASSY,84POS,0.5 SERIES,TYPE1

TE Part #2367837-1
REC CONN CVR ASSY,84POS,0.5 SERIES,TYPE2

Documents

Product Drawings
040III TAB NON SEALED AU

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1565963-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1565963-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1565963-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



MULTILOCK Connector System

English

Product Specifications

Crimping .040III Unsealed Contact, Tab

Japanese

Application Specification

Japanese

Crimping .040III Unsealed Contact, Tab

Japanese

Application Specification

Japanese