





	1	2	3	4											
A	PRODUCT NO	PLATING	Y Y = 0 Y = 1 Y = 2 Y = 3 Y = 4	HOUSING MATERIAL											
	63429-1Y2	0.38um/15u" GOLD OR GXT ON CONTACT AREA OVER 1.27um/50u" Ni (SEE NOTE 7)		30% GLASS FILLED POLYESTER (SEE NOTE 4)											
	63429-2Y2	0.76um/30u" GOLD GXT ON CONTACT AREA OVER 1.27um/50u" Ni (SEE NOTE 7)		30% GLASS FILLED POLYESTER (SEE NOTE 4)											
	63429-3Y2	2.54um/100u" TIN/LEAD OVER 1.27um/50u" Ni		30% GLASS FILLED POLYESTER (SEE NOTE 4)											
	63429-4Y2	GOLD FLASH ON CONTACT AREA OVER 1.27um/50u" Ni		30% GLASS FILLED LCP (SEE NOTE 5)											
B	PRODUCT NO	PLATING	NOTE: 1. MATERIAL 2. PLATING : REFER TO TABLE 3. TECHNICAL REQUIREMENTS: 4. THE HOUSING WILL WITHSTAND EXPOSURE TO 200°C PEAK 5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK 6. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER 7. PLATING OPTION: MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.												
	63429-1Y2LF SEE NOTE 6	0.38um/15u" GOLD OR GXT ON CONTACT AREA OVER 1.27um/50u" Ni (SEE NOTE 7)													
	63429-2Y2LF SEE NOTE 6	0.76um/30u" GOLD OR GXT ON CONTACT AREA OVER 1.27um/50u" Ni (SEE NOTE 7)													
	63429-4Y2LF SEE NOTE 6	GOLD FLASH ON CONTACT AREA OVER 1.27um/50u" Ni													
C			FLAME RETARDANT PER UL 94V-0 TERMINAL : PHOSPHOR BRONZE 2. PLATING : REFER TO TABLE 3. TECHNICAL REQUIREMENTS: INSERTION FORCE : 12 NEWTONS (2.7 LB) MAX. PER CONNECTOR. WITHDRAWL FORCE : 2 NEWTONS (0.45 LB) MIN. PER CONNECTOR. (MATE WITH 0.635MM SQ. PIN 2.54MM PITCH HEADER) 4. THE HOUSING WILL WITHSTAND EXPOSURE TO 200°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN. 5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN. 6. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008. 7. PLATING OPTION: MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.												
D			spec ref tolerance std ISO 406 ISO 1101 ISO 1302	dr eng chr appr	Louis Ng Mike Zhou - Tim Yao	2010/10/11 2018/07/23 - 2018/07/25	projection product family	MM JUMPER	size ecn no rel level	A3 ELX-N-30474-1 Released	scale rev				
					JUMPER		dwg no 63429		Product - Customer Drw		sheet 1 of 1				