






P.C. MOUNTING



O.P. (MM)	P.T. (MM)
14.9 ± 1.2	4.0 MAX


O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



SCHEMATIC - SPDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- ▲ 3. RATING: GOLD; 0.4VA @ 20VAC OR VDC
- ▲ 4. OPERATING FORCE: 75 ± 25 gf
5. OPERATING TEMP: -25°C to 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 mΩ MAX.
- ▲ 11. CONTACTS: 10 MICRO INCHES MINIMUM GOLD PLATING (PN:990001)
12. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-100931	Release	05/04/22	JS	TITLE MS085R105F075V2A				100121860
					SCALE	DATE	DR	DWG	REV
					2:1	4/27/2022	JS	Q970189	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED