



ELECTRICAL CHARACTERISTICS @ 25°C

URNS RATIO

TX 1CT : 1

RX 1CT : 1

QCL @ 100kHz/100mVRMS

8mA DC BIAS 350μH MIN.

INS. LOSS

1MHz TO 100MHz -1.0 dB MAX

RET. LOSS (MIN)

1MHz-30MHz -18 dB

30MHz-60MHz -12 dB

60MHz-80MHz -18+20LOG(F/30MHz) dB

CROSS TALK (TX - RX)

500kHz-1MHz -70 dB MIN

10 MHz -50 dB MIN

30 MHz -45 dB MIN

50 MHz -40 dB MIN

100 MHz -35 dB MIN

CM TO CM REJ

100kHz-1MHz -70 dB MIN

10 MHz -47 dB MIN

30 MHz -42 dB MIN

60 MHz -37 dB MIN

100 MHz -30 dB MIN

CM TO DM REJ

100kHz-1MHz -70 dB MIN

10 MHz -60 dB MIN

30 MHz -50 dB MIN

60 MHz -45 dB MIN

100 MHz -40 dB MIN


HIPOT (Isolation Voltage): 1500 Vrms


100% OF PRODUCTION TESTED TO COMPLY WITH

IEEE 802.3 ISOLATION REQUIREMENTS.

OPERATING TEMPERATURE: 0°C TO +70°C.

SCHEMATIC



ORIGINATED BY CHOW WANCHUNG DATE 2017-06-07	TITLE 1X4 vertical mount MagJack®	PART NO. / DRAWING NO. V8111X4T06-F	STANDARD DIM. TOL. IN INCH	[] METRIC DIM. AS REF.	REV. : B PAGE : 2
DRAWN BY XIE YIMING DATE 2017-06-07	V811-1X4T-06-F	FILE NAME V8111X4T06-F_B.DWG	.X .XX .XXX	UNIT : INCH [mm] SCALE : N/A SIZE : A4	

THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.





RoHS



MECHANICAL SPECIFICATION


NOTES:


PLASTIC HOUSING: THERMOPLASTIC PBT, BLACK
FLAMMABILITY RATING UL 94V-0
CONTACTS: 50 MICRO-INCH HARD GOLD PLATING OR EQUIVALENT.
OUTPUT PINS: TIN-COATED COPPER WIRE, DIA 0.018 INCH, 100 MICRO-INCH MIN MATTE TIN, PINS ARE SOLDER DIPPED.
METAL SHIELD: NICKEL PLATED ON COPPER ALLOY, (ALL GROUND LEADS ARE SOLDER DIPPED)
FRDG LEGS ARE FOR PCB RETENTION FORCE ONLY AND NOT FOR GROUNDING PURPOSE



1. MARK PART WITH MFG LOGO, MFG NAME, PART NUMBER AND DATE CODE.



- 2. THE PRODUCT IS RoHS COMPLIANT.
- 3. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS.
- 4. THE PART IS RECOMMENDED FOR WAVE SOLDERING. THE SUGGESTED PEAK WAVE SOLDERING CONDITION IS 260°C MAX AND 10 SECONDS MAX.



<p>ORIGINATED BY ANTON LIAO DATE 2017-06-07</p> <p>DRAWN BY LI QUANKUN DATE 2017-06-07</p>	<p>TITLE 1X4 vertical mount MagJack® V811-1X4T-06-F</p>	<p>PART NO. / DRAWING NO. V8111X4T06-F</p> <p>FILE NAME V8111X4T06-F_B.DWG</p>	<p>STANDARD DIM. TOL. IN INCH</p> <p>.X .XX .XXX</p>	<p>[] METRIC DIM. AS REF.</p> <p>UNIT : INCH [mm] SCALE : N/A SIZE : A4</p>	<p>REV. : B PAGE : 3</p> 
--	---	--	--	--	---


THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS



RECOMMENDED PCB FOOTPRINT

<COMPONENT SIDE VIEW>



ORIGINATED BY
ANTON LIAO
DATE 2017-06-07

DRAWN BY
LI QUANKUN
DATE 2017-06-07

TITLE
1X4 vertical mount MagJack®
V811-1X4T-06-F

PART NO. / DRAWING NO.
V811X4T06-F

FILE NAME
V811X4T06-F_B.DWG

STANDARD DIM.
TOL. IN INCH

.X
.XX
.XXX

[] METRIC DIM.
AS REF.

UNIT : INCH [mm]
SCALE : N/A
SIZE : A4

REV. : B


PAGE : 4



a bel group

THE INFORMATION CONTAINED HEREIN IS CONSIDERED 'PROPRIETARY' TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS



PACKING INFORMATION

NOTE:

THE DISTANCE OF PANEL INSIDE SURFACE RELATIVE TO FRONT SURFACE OF PART IS ONLY A SUGGESTION. IN CASE THIS DISTANCE IS DIFFERENT, THE REQUIRED PANEL OPENING DIMENSIONS CHANGE ACCORDINGLY.

PACKING TRAY : 0200-9999-A4

PACKING QUANTITY : 25 PCS FINISHED GOODS PER TRAY

10 TRAYS (250 PCS FINISHED GOODS) PER CARTON BOX.

NOTE : CARDBOARD ARE PLACED BETWEEN LAYERS OF PACKING TRAY INSIDE CARTON BOX.
(INCLUDE THE UPPER MOST AND LOWER MOST TRAY)

REV. : B PAGE : 5


ORIGINATED BY
ANTON LIAO
DATE 2017-06-07

DRAWN BY
LI QUANKUN
DATE 2017-06-07

TITLE
1X4 vertical mount MagJack®
V811-1X4T-06-F

PART NO. / DRAWING NO.
V8111X4T06-F
FILE NAME
V8111X4T06-F_B.DWG

STANDARD DIM. TOL. IN INCH		[] METRIC DIM. AS REF.
.X		UNIT : INCH [mm]
.XX		SCALE : N/A
.XXX	±0.004	SIZE : A4



bel MAGNETIC
SOLUTIONS
a bel group