





REV. 0
DCO 143985

COIL: @ 25°C
RESISTANCE 1560 OHMS ±10%
NOMINAL VOLTAGE 26.5 VDC
MUST OPERATE 14.2 VDC
MUST RELEASE 8.0 VDC MAX., 1.37 VDC MIN.

ENVIRONMENT:
VIBRATION 10 Hz TO 3000 Hz @ 30 g's
SHOCK 75 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C
NOTES: OPERATE TIME 2.0 MS MAX.
RELEASE TIME 1.5 MS MAX.
CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 15DEC04 CK. JERRY C. 12/15/04

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/17-036P REV.

"JMGA" RELAY

JMGAC-26P