




REV. 0

DCO 16116

COIL: @ 25°C
 RESISTANCE 27 OHMS ±10%
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 2.7 VDC
 MUST RELEASE 1.65 VDC MAX, 0.29 VDC MIN.

ENVIRONMENT:


VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX

CONTACT STABILIZATION 2.5 MS MAX

ALL OTHER REQUIREMENTS TO MIL-R-39016 LEVEL P

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
 2 AMPS 28 VDC RESISTIVE
 100,000 OPERATIONS

DR. B.D. 2/15/00

CK. 69H 2/15/00



COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. QPL

CUST. NO. M39016/6-139P REV.

"HFW" RELAY

HFW1201L01P