






REVISIONS		DATE	DN	APV
P	LTR	RELEASED	20MAY2019	CJV JW
A		REVISED PER ECN-21-101549	15MAR2021	TX DZ
B		REVISED PER ECN-21-122209	18OCT2021	TM DZ



21.57	5.385	74.76	80.74	38.17	4.57	77.89	76.34	55.86	43.6	58.31	45.6	25.39	21.53	78.89	33.31	4.05	48V
21.07	4.885	73.76	79.74	37.67	3.57	76.89	75.34	54.86	42.6	57.31	44.6	24.39	21.03	77.89	32.31	3.05	12V
T	S	R	P	N	M	L	K	J	H	G	F	E	D	C	B	A	VOLTAGE RATING


THIS DRAWING IS A CONTROLLED DOCUMENT.		DN	22JUN2018	C. VALENTINE	TE Connectivity
DIMENSIONS:	mm	OTHERWISE SPECIFIED:		H. ANDREWS 22JUN2018	
0 PLC	±:	0 PLC	±0.20		
1 PLC	±0.20	1 PLC	±0.20		
2 PLC	±0.20	2 PLC	±0.20		
3 PLC	±0.20	3 PLC	±0.20		
4 PLC	±0.20	4 PLC	±0.20		
APPLICATION SPEC					
MATERIAL	△	ANGLE FINISH	△		
WEIGHT	-				
CUSTOMER DRAWING	A100779	RECEP TACLE ASSEMBLY, 4C WITH HIGH POWER, SLIVER 2.0	2338718	1	
RESTRICTED TO					
SHEET 1 OF 4	6:1	SCALE			
REV C					









THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICA
(C) COPYRIGHT 20 BY -	ALL RIGHTS RESE

RELEASED FOR PUBLICACION
ALL RIGHTS RESERVED

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB OUTLINE DIMENSIONS.
TOLERANCE VALUES ARE CRITICAL. PLEASE BE SURE TO DESIGNATE
TOLERANCES TO PCB SUPPLIER TO ENSURE OPTIMIZED FUNCTIONALITY.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE 22JUN2018	 TE TE Connectivity		
		CHK H. ANDREWS 22JUN2018			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD H. ANDREWS 22JUN2018		
		0 PLC \pm - 1 PLC ± 0.20 2 PLC ± 0.20 3 PLC \pm - 4 PLC \pm -	PRODUCT SPEC - APPLICATION SPEC -		
ANGLES		\pm -			
MATERIAL		FINISH	WEIGHT -		
		CUSTOMER DRAWING			
		SCALE 6 : 1	SHEET 3 OF 4	REV C	
		SIZE A 1	CAGE CODE 00779	DRAWING NO C-2338718	RESTRICTED TO -

REVISIONS					
P	LTR	DESCRIPTION	DATE	DN	APVD
-		SEE SHEET 1	-	-	-

CONTACT NUMBER	SIDE A	SIDE B
1	GROUND	GROUND
2	SIGNAL	SIGNAL
3	SIGNAL	SIGNAL
4	GROUND	GROUND
5	SIGNAL	SIGNAL
6	SIGNAL	SIGNAL
7	GROUND	GROUND
8	SIGNAL	SIGNAL
9	SIGNAL	SIGNAL
10	GROUND	GROUND
11	SIGNAL	SIGNAL
12	SIGNAL	SIGNAL
13	GROUND	GROUND
14	SIGNAL	SIGNAL
15	SIGNAL	SIGNAL
16	GROUND	GROUND
17	SIGNAL	SIGNAL
18	SIGNAL	SIGNAL
19	GROUND	GROUND
20	SIGNAL	SIGNAL
21	SIGNAL	SIGNAL
22	GROUND	GROUND
23	SIGNAL	SIGNAL
24	SIGNAL	SIGNAL
25	GROUND	GROUND
26	SIGNAL	SIGNAL
27	SIGNAL	SIGNAL
28	GROUND	GROUND
29	GROUND	GROUND
30	SIGNAL	SIGNAL
31	SIGNAL	SIGNAL
32	GROUND	GROUND
33	SIGNAL	SIGNAL
34	SIGNAL	SIGNAL
35	GROUND	GROUND
36	SIGNAL	SIGNAL
37	SIGNAL	SIGNAL
38	GROUND	GROUND
39	SIGNAL	SIGNAL
40	SIGNAL	SIGNAL
41	GROUND	GROUND
42	GROUND	GROUND
43	GROUND	GROUND
44	SIGNAL	SIGNAL
45	SIGNAL	SIGNAL
46	GROUND	GROUND
47	SIGNAL	SIGNAL
48	SIGNAL	SIGNAL
49	GROUND	GROUND
50	SIGNAL	SIGNAL
51	SIGNAL	SIGNAL
52	GROUND	GROUND
53	SIGNAL	SIGNAL
54	SIGNAL	SIGNAL
55	GROUND	GROUND
56	SIGNAL	SIGNAL
57	SIGNAL	SIGNAL
58	GROUND	GROUND
59	SIGNAL	SIGNAL
60	SIGNAL	SIGNAL
61	GROUND	GROUND
62	SIGNAL	SIGNAL
63	SIGNAL	SIGNAL
64	GROUND	GROUND
65	SIGNAL	SIGNAL
66	SIGNAL	SIGNAL
67	GROUND	GROUND
68	SIGNAL	SIGNAL
69	SIGNAL	SIGNAL
70	GROUND	GROUND

CONTACT NUMBER	SIDE A	SIDE B
36	SIGNAL	SIGNAL
37	SIGNAL	SIGNAL
38	GROUND	GROUND
39	SIGNAL	SIGNAL
40	SIGNAL	SIGNAL
41	GROUND	GROUND
42	GROUND	GROUND
43	GROUND	GROUND
44	SIGNAL	SIGNAL
45	SIGNAL	SIGNAL
46	GROUND	GROUND
47	SIGNAL	SIGNAL
48	SIGNAL	SIGNAL
49	GROUND	GROUND
50	SIGNAL	SIGNAL
51	SIGNAL	SIGNAL
52	GROUND	GROUND
53	SIGNAL	SIGNAL
54	SIGNAL	SIGNAL
55	GROUND	GROUND
56	SIGNAL	SIGNAL
57	SIGNAL	SIGNAL
58	GROUND	GROUND
59	SIGNAL	SIGNAL
60	SIGNAL	SIGNAL
61	GROUND	GROUND
62	SIGNAL	SIGNAL
63	SIGNAL	SIGNAL
64	GROUND	GROUND
65	SIGNAL	SIGNAL
66	SIGNAL	SIGNAL
67	GROUND	GROUND
68	SIGNAL	SIGNAL
69	SIGNAL	SIGNAL
70	GROUND	GROUND




FIGURE 1
SOFT TRAY PACKAGING
2338718-1 AND 2338718-2
SCALE 3:4




FIGURE 2
HARD TRAY PACKAGING
2338718-3 TO 1-2338718-0
SCALE 3:4

THIS DRAWING IS A CONTROLLED DOCUMENT.		22 JUN 2018	C. VALENTINE
		CH- ANDREWS 22 JUN 2018	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		0 PLC	±:
		1 PLC	±0.20
		2 PLC	±0.20
		3 PLC	±:
		4 PLC	±:
MATERIAL		APPLICATION SPEC	
		FINISH	
WEIGHT		CAGE CODE DRAWING NO	
A1 00779 C=2338718		A 100779 C=2338718	
CUSTOMER DRAWING		SCALE 6:1	RESTRICTED TO
		4 OF 4	-
		REV C	