




PANEL CUTOUT

PANEL THICKNESS	(X) DIM.
0.75 to 1.25	20.2mm
1.25 to 2.00	20.4mm
2.00 to 3.00	20.6mm




SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OPEN	2-1



CIRCUIT: SPST

NOTE:

- DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- CONTACT RATING: ANSI/UL 1054 CAN/USA C22.2 NO. 55 (E194579):
16A @ 125VAC [UR, cUR]
10A @ 250VAC [UR, cUR]
1/3 HP 125/250VAC [UR, cUR]
EN 61058-1: 2002:
10(4)A 250~ μ 1E4 T125/55 [ENEC14]
10(2)A 250~ μ 5E4 T85/55 [ENEC14]
- CONTACT RESISTANCE: 35m Ω MAX. @ 50VAC
- INSULATION RESISTANCE: 100M Ω MIN. @ 500VAC
- DIELECTRIC STRENGTH: 1,500VAC FOR 1 MINUTE
- ELECTRICAL LIFE: 6,000 CYCLES [UR, cUR]
10,000 CYCLES [ENEC14: 10(4)A 250V~]
50,000 CYCLES [ENEC14: 10(2)A 250V~]
- OPERATING TEMP.: -20°C to 105°C [UR, cUR]
-20°C to 125°C [ENEC14: 10(4)A 250V~]
-20°C to 85°C [ENEC14: 10(2)A 250V~]
- ▲ DENOTES CRITICAL PARAMETER
- ILLUMINATION VOLTAGE: 250V



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-101213	Release	08/31/22	MW	TITLE RR111C1000-117				100122658
					SCALE	DATE	DR	DWG	REV
					2:1	8/30/2022	MW	38-RR111C1000117	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED