


1	2	3	4					5					
		YAZAKI PART NO. AND CH. CODE	C	D	E	W ₁	R ₁	W ₂	R ₂	Δ H ₁	Δ H ₂	WIRE SIZE	MATERIAL
		7116-2951, <u>A</u>	4.00	1.70	7.50	3.60	0.70	5.30	1.60	(3.90)	(4.70)	AVS 0.85~2.00 EQUIVALENT	Δ BRASS, t=0.40
		7116-2951-02, <u>A</u>	//	//	//	//	//	//	//	//	//	//	Δ BRASS, t=0.40
		7116-2952, <u>A</u>	3.00	1.70	6.50	2.40	0.40	3.90	1.10	(2.80)	(3.43)	AVS 0.70~0.50 EQUIVALENT	Δ TIN PLATE
		7116-2952-02, <u>A</u>	//	//	//	//	//	//	//	//	//	//	Δ BRASS, t=0.40
			//	//	//	//	//	//	//	//	//	//	Δ TIN PLATE



CUSTOMER	CUSTOMER PART NO.	CUSTOMER DNG NO.	MATL. SPEC.	SEE TABLE	TREAT. & F IN.	ISSUE MARK
OFFICE						
VENDOR						
VENDOR NO.						
DNG TYPE	DNG SOURCE	DNG DATE	UNIT	SCL	ANGLE	
A R	NEW	1990/12/13	mm	5:1	3	
APPROVED	CHECKED	DESIGN	DRAWN			
K. SUZUKI	H. SHIBATA		KAMEYAMA	J. CANDO		
2013/02/21	2013/02/21	1990/12/13	2013/02/21			
3	4	5				

GENERAL TOLERANCE	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	O. 1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	O. 1
C	±0.3	±0.5	±0.8	±1.4	±2	±30°	O. 15
SPECIFIED						MASS	

Δ	2013/02/21	UPDATE OF DRAWING ETC.	C13-2096	J C
Δ	2002/04/12	CHANGED DIMENSION	C02-X446	K. S
Δ	1995/10/02	CHANGED FORM. A	C95-M553	Y. Y
Δ	1992/08/20	ADDITIONAL APPLICABLE	C92-6802	I. K
Δ	1990/12/13	NEW	C90-7811	I. K
LET	DATE	REVISION RECORD	NO.	CHD

PART NO.	7116-2951 ETC.
CH. CODE	
DWG NO.	7116-2951: R
SET DWG NO.	
YAZAKI CORPORATION	