






SUGGESTED PANEL CUTOUT

CIRCUIT: SPST
OFF - ON

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
- ▲ 4. RATING: 15A @125VAC [cURus]
5. MATERIAL:
CONTACT SURFACE: SILVER PLATED COPPER
TERMINAL: BRASS ALLOY w/SILVER PLATE
6. ELECTRICAL LIFE: 10,000 CYCLES MIN.
7. CONTACT RESISTANCE: 20 Milli-OHMS MAX.
8. OPERATING TEMP: -20°C TO 65°C [cURus, CSA]
-20°C TO 105°C [cURus]
9. DIELECTRIC STRENGTH: >1,000VAC 1MIN
10. LAMP VOLTAGE: 125V
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. LENS COLOR, RED



REV	ECO NO	DESCRIPTION	DATE	BY
A	ECO-100948	RELEASE	05/05/22	JS



E-SWITCH®

OBJECT ID
100121871

TITLE RSC211C1021-116

SCALE
3:2DATE
5/2/2022DR
JSDWG
38-RSC211C1021116REV
ATHE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED