




OSSM
JACK


.190-36, UNS-2A
TYP

.250 HEX
6.4

NOTES:
1. CAPTURED CENTER CONTACT

.XXX = in
XX.X = mm

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₁	REDRAWN ON CAD ECN 94-0474 <i>PRB</i>	1/17/95	<i>PRB</i> 1/17/95



RECOMMENDED
MOUNTING HOLE

HOUSING MOUNTING NUT LOCKWASHER			STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303			GOLD PLATE PER MIL-G-45204				
DIELECTRIC			TFE FLUOROCARBON PER ASTM-D-1457			N/A				
CENTER CONTACT			BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H			GOLD PLATE PER MIL-G-45204				
COMPONENT			MATERIAL			FINISH				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°			DRAWN BY EJC 7/24/68		 AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599					
			CHECKED BY PRB 7/24/68							
			APPD BY EJD 8/12/68							
These drawings and speci- fications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale o f item(s) without written permission.			USE ASS'Y PROCEDURE NO. A.P. <u> </u>		TITLE OSSM BULKHEAD FEEDTHRU JACK RECEPTACLE-SOLDER TERMINAL					
					SIZE B	CODE IDENT NO. 26805	1058-0000-00		REV 01 ₁	
					SCALE 10/1				SHEET 1 OF 1	

COPY IN PUERTO RICO

CUSTOMER DRAWING

AMP PART # 1045636-1
SHEET 1 OF 1 REV A