

FEATURES

- * Low forward voltage drop
- * High current capability
- * High reliability
- * Low Power Loss, High Efficiency
- * Ultrafast 35 and 60 Nanosecond Recovery times

MECHANICAL DATA

- * Case: Molded plastic
- * Epoxy: UL 94V-0 rate flame retardant
- * Lead: Axial leads, solderable per MIL-STD-202, method 208 guaranteed
- * Polarity: Color band denotes cathode end
- * Mounting position: Any
- * Weight: 1.98 grams


VOLTAGE RANGE

100 to 600 Volts

CURRENT

10.0 Ampere

TO-220AB



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

- * Rating at 25 °C ambient temperature unless otherwise specified.
- * Single phase, half wave, 60 Hz, resistive or inductive load.
- * For capacitive load, derate current by 20%

Type Number	Symbol	MUR 1010CT	MUR 1020CT	MUR 1040CT	MUR 1060CT	Unit
Maximum Repetitive Peak Reverse Voltage	VRRM	100	200	400	600	V
Maximum RMS Voltage	VRMS	70	140	280	420	V
Maximum DC Blocking Voltage	VDC	100	200	400	600	V
Maximum Average Forward Rectified Current	IF	10				A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	IFSM	80A				A
Maximum Instantaneous Forward Voltage @5A	VF	1.0		1.3	1.7	v
Maximum Reverse Current @ Rated VR TA=25 °C TA=125 °C	IR	10 500				uA
Typical Junction Capacitance (Note 1)	Cj	150				pF
Typical Thermal Resistance(Note 2)	RθJA	30				°C/w
Operating and Storage Temperature Range	TJ	-65~+150				°C
Maximum reverse recovery time (Note 3)	Trr	35				nS

NOTE1. Measured at 1.0 MHz and applied reverse voltage of 4.0V D.C.

NOTE2. Leads maintained at ambient temperature at a distance of 9.5mm from the case

NOTE3. Measured with IF = 0.5A, IR = 1.0A, IRR = 0.25A. See figure 5.

RATINGS AND CHARACTERISTIC CURVES

FIG.1 MAXIMUM FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 5 TYPICAL JUNCTION CAPACITANCE




FIG. 4 TYPICAL REVERSE CHARACTERISTICS





FIG. 3 TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS



Packge	Pcking	Box Size L×W×H(mm)	Quatity(pcs/box)	Carton Size L×W×H(mm)	Quatity(pcs/carton)
TO-220AB	50pcs/Tube	558×148×38	1000	565×225×170	5000