





REV, 2 8/25/98

COIL: @ 25°C
 RESISTANCE 1560 OHMS ± 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 14.2 VDC
 GATE TURN-ON 4.3 VDC MAX.
 GATE TURN-OFF 0.5 VDC MAX.
 MUST RELEASE 8.0 VDC MAX, 1.30 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.5 MS MAX.
 RELEASE TIME 4.0 MS MAX.
 CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 3/5/97 *(Signature)* 8/25/98

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. GPL
 CUST. NO. M28776/6-006M

TYPE JMGAT RELAY

JMGAT-26M