








PART NUMBER
SEE NOTE 6



SCALE
3.000
RECOMMENDED PCB LAYOUT (THICKNESS=1.2MM)
TOLERANCE ±0.05

- NOTES:
- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMAL PLASTIC,
UL94V-0, BLACK.
TERMINAL: COPPER ALLOY.
SHELL: COPPER ALLOY.
 - FINISH:
TERMINAL:
30u" GXT/Au ON CONTACT AREA.
100u" MATTE TIN ON SOLDER TAIL.
UNDER PLATING: 50u" Ni MIN. OVER ALL.
SHELL:
MATTE TIN OVER 50u" Ni OVER ALL.
100u" MATTE TIN MIN ON SOLDER TAIL OVER 50u" Ni.
 - THIS PRODUCT WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN;
 - FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
 - THE PRODUCT CAN BE USED FOR PIP PROCESS.
 - PART NUMBER DEFINITION:
10126196 - X 0X X LF
- LEAD FREE
PACKING TYPE
B: TUBE
R: TAPE & REEL
01: DIM A=2.54
02: DIM A=2.00
PLATING CODE
1: 30u" GXT ON CONTACT AREA
2: 30u" Au ON CONTACT AREA

spec ref		-		dr		John Han		2013/07/17		projection				MM		size		A3		scale		1.000	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Laurence Zang		2017/11/20						ecn no		ELX-N-28523-1							
ISO 406																							
ISO 1101																							
				chr		-		-		product family		-		rel level		Released							
				appr		Tim Yao		2017/11/22															
surface 		linear		0.X		±0.3		Amphenol FCI		title		USB 2.0 A TYPE RECEPTACLE		dwg no		10126196		rev		C			
				0.XX		±0.20																	
				0.XXX		±0.10																	
ISO 1302		angular		0°		±2°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 1 of 1							