









RECOMMENDED PCB LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. RATING: 12VDC, 50mA MAX.
4. CONTACT RESISTANCE: 500m Ω MAX.
5. INSULATION RESISTANCE: 100M Ω MIN. @ 100VDC
6. TRAVEL: 0.2 ± 0.1 mm
7. DIELECTRIC STRENGTH: 250V AC FOR 1 MIN.
- ▲ 8. OPERATING FORCE: 160 ± 50 gf
9. OPERATING TEMPERATURE: -40°C TO 85°C
10. OPERATING LIFE: 100,000 CYCLES.
11. PACKAGING: TAPE & REEL, 1400 PIECES PER REEL
12. ▲ DENOTES CRITICAL PARAMETER
- ▲ 13. CONTACT MATERIAL: GOLD FLASH



LED SPECS	UNITS	GREEN	YELLOW
FORWARD CURRENT	mA	20	20
FORWARD VOLTAGE	V	3.20 typ.	2.00 typ.
LUMINOUS INTENSITY	mcd	150 typ.	180 typ.
PEAK WAVELENGTH	nm	525	590

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH® OBJECT ID 100122167				
C	ECO-101968	NOTE 13: GOLD FLASH WAS GOLD	05/24/23	JS	TITLE TL3275AF160GYR				
B	ECO-101393	ADD L1 GREEN & L2 YELLOW TO SCHEMATIC	11/07/22	MR					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 8:1	DATE 9/16/2022	DR MJR	DWG B327511	REV C