


- NOTES:
- 1

PACK IN ACCORDANCE WITH TE SPEC 107-3275
- 2

Au PLATING: 50u”
- 3

Passivation
- 4 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Frequency Range (GHz) DC to 18GHz	Recommended Coupling Torque N/A	Temperature Rating -40°C TO +85°C
Voltage Rating (Peak) @ Sea Level 500 V RMS	Mating cycles 500 cycles	
Insulation Resistance (MIN.) 5000 M ohms	Center contact retention force 6 lbs MIN	
Contact Resistance (Milliohms MAX) Center Contact 1.0 Outer Contact 0.4	VSWR: 1.2 Max @ DC-- 18 GHz	
Dielectric Withstand Voltage: 1500 V RMS Max	RF leakage:	N/A
Insertion Loss : 0.1*√F(GHz) dB	3rd Intermodulation:	N/A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± 0.2
2 PLC ± 0.1
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN ED 13JUN 2018
CHK BW 13JUN 2018
APVD RS 13JUN 2018

PRODUCT SPEC
APPLICATION SPEC
WEIGHT 0.000000

CUSTOMER DRAWING

2	PVC (BLACK)	DUST CAP	4
1	PEI	INSULATION	3
1	BECU	CENTER CONTACT	2
1	STEEL	BODY	1
-1	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY		PARTS LIST	
TE Connectivity			
NAME ADAPTER N Female to N Female			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2081562	-
SCALE 3:1		SHEET 1 OF 1	REV A1