




PART NO. AND CH. CODE	W1	TREAT. & FIN.	APPRICABLE WIRE SIZE
7116-4618-02	1.82	TIN PLATING	AWG 22~20 CABLE DIAMETER 1.20~1.90 $\triangle$
7116-4619-02	1.96	TIN PLATING	AWG 18 CABLE DIAMETER 1.50~1.90 $\triangle$
$\triangle$ 7116-4618-08	1.82	GOLD PLATING	AWG 22~20 CABLE DIAMETER 1.20~1.90
$\triangle$ 7116-4619-08	1.96	GOLD PLATING	AWG 18 CABLE DIAMETER 1.50~1.90
$\triangle$ 7116-5231-08 (7B16-5231-08)	1.82	GOLD PLATING	AWG 22~20 CABLE DIAMETER 1.20~1.90
$\triangle$ 7116-5232-08 (7B16-5232-08)	1.96	GOLD PLATING	AWG 18 CABLE DIAMETER 1.50~1.90


$\triangle$ 注記

- 嵌合端子品番 TIN: 7114-4618-02 ETC.
GOLD: -
- () 内品番は、エアバッグ (A/B) 回路及び特別回路に使用時に適用する。


$\triangle$ NOTES

- MALE COUNTERPART NO. TIN: 7114-4618-02 ETC.
GOLD: -
- () PART NO IS USED FOR PARTS ASSOCIATED WITH
A/B CIRCUITS OR OTHER SPECIFIED CIRCUITS.

GOLD PLATING AREA FOR 7116-5231-08, 7116-5232-08
(7B16-5231-08, 7B16-5232-08)



GOLD FLASH PLATING AREA FOR 7116-4618-08,
7116-4619-08



△	07/09/11	CHANGED NOTES, ETC.	C07-Z899	T. Y
△	06/11/23	ADDED PART NO., ETC.	C06-ZC98	T. Y
△	03/10/15	NEW	C03-X622	Y. I
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1
③	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15
SPECIFIED						MASS	

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.		MATERIAL SPEC.		TREAT. & FIN.	
OFFICE		VENDOR		TRIAL PART NO.		NAME		KAIZEN 0.64 TERMINAL FEMALE	
DWG TYPE		DWG SOURCE		DWG DATE		UNIT		SCL	
R		NEW		03/10/15		mm		5:1	
APPROVED		CHECKED		DESIGN		DRAWN		PART NO.	
Y. ITO		Y. ITO		Y. ITO		A. PANGANIBAN		7116-4618-02 ETC.	
07.09.12		07.09.12		07.09.11		03/09/11		07/09/11	
								DWG NO.	
								7116-4618-02:R	
								SET DWG NO.	
								YAZAKI CORPORATION	