




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H2	REVISED AS PER ECO-20-003569.	11MAR2020	TC	NP



NOTES:

1. PART DESCRIPTION: CONNECTOR, PLUG SUBMINIATURE, TRIAXIAL (RAYTHEON # 114453046) COMPLETE WITH PREFLUXED SOLDER PREFORM RING AND HEAT SHRINKABLE SLEEVE.

MATERIAL:

HOUSING BODY: BRASS ALLOY PER ASTM B16 (QQ-B-626)
 COUPLING NUT: STAINLESS STEEL, TYPE 303 PER ASTM A582.
 INSULATING SLEEVE: HEAT SHRINKABLE, POLYVINYLIDENE FLUORIDE (TRANSPARENT BLUE)
 SOLDER RING: PREFLUXED SOLDER PREFORM, COMPOSITION Sn63, ROLO FLUX PER ANSI-J-STD-004.
 INSULATOR: THERMOPLASTIC PER LP 392.

FINISH:

HOUSING BODY: TIN PLATED PER MIL-T-10727
 COUPLING NUT: PASSIVATED PER QQ-P-35B.

2. HOUSING ACCOMMODATION: HOUSING DESIGNED TO ACCEPT SHIELDED CONTACTS MIS-20067/1 THRU MIS-20067/4 SHIELDED, RAYCHEM SOLDER TACT D-602-44/45 AND D-602-54/55.
3. WIRE SIZE: HOUSING WILL TERMINATE OUTER SHIELD OF TRIAX/TWINAX CABLE HAVING A SHIELD DIA. OF .185 MAX.
4. MATING CONNECTORS: THIS CONNECTOR WILL MATE WITH D-621-0002 (RAYTHEON# 11453047) AND D-621-0003 (RAYTHEON# 11453048) CONNECTOR, JACK, TRIAXIAL, BULKHEAD.

- (5) ITEMS SUPPLIED AS PART OF CONNECTOR ASSEMBLY.
 (6) RECOMMENDED TWINAX STRIPPING TOOL AD-1479 OR AD-1496.
 (7) SEE PROCEDURE ES 61124 FOR TERMINATION INFORMATION.

ACCESSORIES (5) (7)


CTA-0012	BARRIER TUBE
CTA-0013	PREFORM INSULATOR SLEEVES (2)
D-600-0024	STRAIN RELIEF

DIMENSIONS:

INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± 0.01
3 PLC	± 0.005
4 PLC	± -
ANGLES	± -



DWN	T. CORREIA	11MAR2020
CHK	R. MACNAUGHTON	11MAR2020
APVD	N. PRZYBYLSKA	11MAR2020

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

MATERIAL

—

FINISH

—



TE Connectivity

NAME

CONNECTOR, PLUG
SUBMINIATURE, TRIAXIAL

SIZE

A4

CAGE CODE

06090

DRAWING NO

C-D-621-0001

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 1

REV

H2