

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT20


BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D8	PN 5-2 AND 5-6 RELEASED FOR PRODUCTION	07DEC2018	RK	PS
	D9	PART OBSOLETE	28AUG2020	DV	PS

POLARIZATION KEY SLOT




CLAMPING SCREW




1546108-3 AS SHOWN

WIRE ENTRY



5.08±0.08
TYP

2.54 REF
2 PLC



15.5

18.4

RETENTION LATCH

MATING FACE

10	OBSOLETE	BLACK	DETAIL N	TIN	30.48±0.20	6	6-1546108-9
		GREEN	DETAIL M	TIN	15.24±0.15	3	6-1546108-8
		ORANGE	DETAIL M	TIN	15.24±0.15	3	6-1546108-7
		BLACK	DETAIL M	TIN	15.24±0.15	3	6-1546108-6
		BLACK	DETAIL N	TIN	25.40±0.20	5	6-1546108-5
		GREEN	DETAIL N	TIN	15.24±0.15	3	6-1546108-4
		ORANGE	DETAIL N	TIN	15.24±0.15	3	6-1546108-3
		BLACK	DETAIL N	TIN	15.24±0.15	3	6-1546108-2
	OBSOLETE	GRAY	DETAIL H	TIN	55.88	11	5-1546108-1
		GRAY	DETAIL H	TIN	45.72	9	5-1546108-9
		GRAY	DETAIL H	TIN	30.48±0.20	6	5-1546108-6
		GRAY	DETAIL H	TIN	20.32±0.15	4	5-1546108-4
		GRAY	DETAIL H	TIN	15.24±0.15	3	5-1546108-3
		GRAY	DETAIL H	TIN	10.16±0.15	2	5-1546108-2
9	OBSOLETE	GRAY	DETAIL H	TIN	60.96	12	4-1546108-7
		GRAY	-	TIN	15.24±0.15	3	4-1546108-6
		GRAY	DETAIL K	TIN	40.64	8	4-1546108-5
		GRAY	DETAIL H	TIN	40.64	8	4-1546108-4
	OBSOLETE	GRAY	DETAIL H	TIN	96.52±0.35	19	4-1546108-3
		GRAY			60.96±0.20	12	4-1546108-2
		GRAY			30.48±0.20	6	3-1546108-6
		GRAY			20.32±0.15	4	3-1546108-4
	OBSOLETE	GRAY			15.24±0.15	3	3-1546108-3
		GRAY		TIN	127.00±0.35	25	2-1546108-5
		GRAY		TIN	121.92±0.35	24	2-1546108-4
	OBSOLETE	GRAY		TIN	116.84±0.35	23	2-1546108-3
		GRAY		TIN	111.76±0.35	22	2-1546108-2
		GRAY		TIN	106.68±0.35	21	2-1546108-1
		GRAY		TIN	101.60±0.35	20	2-1546108-0
		GRAY		TIN	96.52±0.35	19	1-1546108-9
		GRAY		TIN	91.44±0.30	18	1-1546108-8
		GRAY		TIN	86.36±0.30	17	1-1546108-7
	OBSOLETE	GRAY		TIN	81.28±0.30	16	1-1546108-6
		GRAY		TIN	76.20±0.30	15	1-1546108-5
		GRAY		TIN	71.12	14	1-1546108-4
		GRAY		TIN	66.04	13	1-1546108-3
		GRAY		TIN	60.96	12	1-1546108-2
	OBSOLETE	GRAY		TIN	55.88	11	1-1546108-1
		GRAY		TIN	50.80	10	1-1546108-0
		GRAY		TIN	45.72	9	1-1546108-9
	OBSOLETE	GRAY		TIN	40.64	8	1-1546108-8
		GRAY		TIN	35.56±0.20	7	1-1546108-7
		GRAY		TIN	30.48±0.20	6	1-1546108-6
	OBSOLETE	GRAY		TIN	25.40±0.20	5	1-1546108-5
		GRAY		TIN	20.32±0.15	4	1-1546108-4
	OBSOLETE	GRAY		TIN	15.24±0.15	3	1-1546108-3
		GRAY		TIN	10.16±0.15	2	1-1546108-2
		COLOR	MARKING STYLE	CONTACT FINISH	L	NO OF POSN	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S.WELDON
11SEP2002

CHK
C.RICHARD
11SEP2002

APVD
C.RICHARD
11SEP2002

DIMENSIONS:
mm



0 PLC ±

1 PLC ±0.3

2 PLC ±0.25

3 PLC ±

4 PLC ±

ANGLES ±2°

FINISH

MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
SEE NOTES

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

NAME
TERMINAL BLOCK, PLUG, STACKING,
5.08mm PITCH

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1546108

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 2

REV
D9

1471-9 (3/13)



1

2

3

4

		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



10 WITH STRAIN RELIEF

1471-9 (3/13)