









PAPT NO	L
SS-3235D-01-L1	2.0
SS-3235D-01-L2	3.0
SS-3235D-01-L3	4.0
SS-3235D-01-L4	5.0



NOTE:
Rating:DC 12V 50mA
Insulation resistance:100mΩ(DC100V)
Withstanding voltage:AC100V/minute
Operating temperature:-10℃~+60℃
Force:200gf±100gf
Lifetime:10000 Cycles

Lid	1	SUS	Silvery white
Contact spring	2	Phosphor Bronze	Silver plating
Keystake	1	PPA	Black
Base	1	PPA Brass	Black Silver plating
PAPT NAME	QTY	MATERIAL	FINISHING

广东星坤科技股份有限公司

Δx

Δx

Δx

MARK

日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ANGLAR	±5°			
L ≤ 4	±0.2			
4 < L ≤ 16	±0.3			
16 < L ≤ 63	±0.4			
L > 63	±0.5			



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE: SLIDE SWITCH
DWN	VIEW:	PART NO.: SS-3235D-01-X
CHKD	UNIT: mm/in	DWG NO.: X-SS-3235D-01-X
APPD	SIZE: A4	
WEIGHT	SHEET	REVISION
	1/1	A0