




P.C.B LAYOUT

规格 Specifications:

额定电压 Voltage rating:250VAC/DC。

额定电流 Current rating:3A AC/DC

耐电压 Withstanding voltage:1000V AC/minute

温度区间 Temperature range:-40℃to+105℃

绝缘电阻 Insulation resistance: $\geq 1000\text{M}\Omega$ Min

接触电阻 Contact resistance: $\leq 20\text{M}\Omega$ Max

材料 Material: PA6T UL94V-0


镀层 Planting Category: 1U"Gold

回流焊温度 Reflow soldering temperature: $260 \pm 5^{\circ}\text{C}$, 10s

X6521 F V S - 2xXX - C71 D66
 (1) (2) (3) (4) (5) (6) (7)

- 1.Series No.
- 2.Category:F-Female
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way S-SMT
- 5.Row No -Pin No:2xXX-2x02P-2x40P
- 6.Plastic height: C=7.1mm
- 7.Plastic length:D=6.6mm

X6521FRS-2xXX-C71D66	PA6T UL94V-0	Brass	1U"Gold	X6521W
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Water

广东星坤科技股份有限公司										DSND			SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connector											
Δx				日期				ANGLAR		±5°		DWN		VIEW: 	PART NO.: X6521FVS-2xXX-C71D66										
Δx								L≤ 4		±0.2		CHKD		UNIT: mm/in	DWG NO.: X-X6521FVS-2xXX-C71D66										
Δx								4<L≤ 16		±0.3		APPD		SIZE: A4											
Δx								16<L≤ 63		±0.4															
MARK				DESCRIPTION		DATE		REVISED		APPROVED		L> 63		±0.5		UNSPECIFIED TOLERANCES									
文件工程章										REVISIONS					XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT		SHEET		REVISION	
										www.helloxkb.com www.helloxkb.cn www.xk-dg.cn												1/1		A0	