







PCB LAYOUT





▲ CIRCUIT DIAGRAM

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RATING: CURRENT: 100mA
VOLTAGE: 30 VDC
5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 500VDC, 100M Ω . MIN.
7. OPERATING FORCE: 250gf $\pm$ 100 GRAMS
8. OPERATING TEMP.: -40°C to 85°C
- ▲ 9. TRAVEL: MOMENTARY
1.50 $\pm$ 0.3mm FULL TRAVEL
10. CONTACT RESISTANCE: 50 m Ω . MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. LED COLOR: NO LED



NO ACTUATOR CAP



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-100730	NEW RELEASE	02/10/22	MR	TITLE LP4OA1PBNNN				100121001
					SCALE	DATE	DR	DWG	REV
					2:1	4/6/2016	MJR	B240068	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED