

4		3		2		1		
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.				ALL INTERNATIONAL RIGHTS RESERVED.				
LOC G		DIST 14		REVISIONS				
P		LTR		DESCRIPTION		DATE	DWN	APVD
		G1		REVISED PER ECR-09-019194		01SEP09	HMR	TM

1

STAMP AMP 22-18 APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16

2 WIRE INSUL DIA, 2.67-3.56[.105-.140]

3 TONGUE MATL THK, 0.79±0.05[.031±.002]

BODY

SLEEVE
COLOR, ORANGE

SERRATION

5.00±0.08 DIA
[.197±.003]
(FOR #10 STUD)

7.14
[.281]

6.35
[.250] MIN

15.52
[.611] MAX

19.02
[.749] MAX

1

5000		ON TAPE, REEL		2-321894-1	
1000		LOOSE PIECE		321894	
QTY		PACKAGE TYPE		PART NO	

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: 649°C [1200°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L OLMEDA 100CT94		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK M ELLIS 100CT94	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		VOLTAGE RATING: -		0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -		APVD S BORTNER 100CT94	
FOR ORDER ENTRY		1-800-526-5142		CIRCULAR MIL AREA: 0.26mm²-1.65mm² [509-3260]		MATERIAL BODY, NI PER ASTM B162 SLEEVE, NI SIL PER ASTM B122		PRODUCT SPEC -	
		STRANDED WIRE						APPLICATION SPEC -	
								WEIGHT -	
								CUSTOMER DRAWING	

NAME TERMINAL, RING TONGUE, STRATOTHERM, DIAMOND GRIP, WIRE SIZE, 22-16 AWG		SIZE A3		CAGE CODE 00779		DRAWING NO C-321894		RESTRICTED TO -	
SCALE 6:1		SHEET 1 OF 1		REV G1					