





REV.	DATE	ECR NO.	DESCRIPTION
NC	04/02/01	XXXXXX	INITIAL RELEASE
A	02/03/10	2020	ADDED RECOMMENDED PCB LAYOUT
B	07/11/11	2197	CHANGE THE DESCRIPTION TO " SMA END LAUNCH RECEPT. JACK"



RECOMMENDED PCB LAYOUT



BOTTOM VIEW



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING					APPROVALS		DATE		Amphenol Connex					
					DRAWN		M.ZHANG						07/11/11	
					CHECKED				PART DESCRIPTION SMA END LAUNCH RECEPT. JACK (.042” BOARD THICKNESS)					
					ISSUED									
SHEET		1 OF 1				PART NO. 132323								
CAD FILE		C:/CONNEX/132323.DWG		DWG. NO.		132323.DWG		REV.		B	SIZE	A	SCALE	NA

Amphenol Connex

SMA END LAUNCH RECEPT. JACK
(.042" BOARD THICKNESS)

132323

DWG. NO. 132323.DWG

REV. B

SIZE A

SCALE NA