


2		3				
TABLE 1	SUB ASSEMBLY PART NO.	NO.	PART NO.	MATERIAL	COLOR	QTY.
A	7283-1198 ETC.	①	SEE TABLE 2	A PBT	SEE TABLE 2	1
		②	7157-4052	A PBT	NATURAL A	1

TABLE 2

SUB ASSEMBLY PART NO.	PART NO.	COLOR
7283-1198, ㊦	7183-1198	NATURAL
7283-1198-10, ㊦	7183-1198-10	DARK GRAY
7283-1198-30, ㊦	7183-1198-30	BLACK
7283-1198-40, ㊦	7183-1198-40	LIGHT GRAY
7283-1198-50, ㊦	7183-1198-50	ORANGE
7283-1198-60, ㊦	7183-1198-60	GREEN
7283-1198-80, ㊦	7183-1198-80	BROWN
7283-1198-90, ㊦	7183-1198-90	BLUE

注 記

- 1) 嵌合相手品番 : 7282-1198 ETC.
2) 適用端子品番 : 090Ⅱ 7116-4020 ETC.
187 7116-4030 ETC.

NOTES

- 1) MATING PART NO.: 7282-1198 ETC.
2) APPLICABLE TERMINAL NO. : 090Ⅱ 7116-4020 ETC.
187 7116-4030 ETC.

A 97.12.11 CHANGED MATERIAL C97-N743 H.K																
A 96.06.24 CHANGED MATERIAL, A C96-M146 H.K												ISSUE MARK				
A 90.11.10 CHANGED SPACER COLOR C90-M207 M.H				CUSTOMER				MATL. SPEC. SEE TABLE 1				TREAT. & FIN.				
A 90.02.13 ADDED PART NO. C90-L186 K.M				CUSTOMER PART NO.				CUSTOMER DWG NO.								
A 89.09.07 ADDED PART NO. C89-L958 M.H												NAME 090II 18P+187 1P HYBRID				
88.12.24 NEW C89-L038 K.J				OFFICE				TRIAL PART NO.								
LET DATE REVISION RECORD NO. CHKD				VENDOR												
GENERAL TOLERANCE				VENDOR NO.								CONNECTOR SUB ASSEMBLY FEMALE				
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SOL	ANGLE	PART NO.		
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1	R	NEW	89.01.13	mm	2/1	3	7283-1198 ETC.		
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN				
C	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15	加藤	山梨	梁三輪	Y.OHTA	SERISAWA		DWG NO. 7283-1198: R	SET DWG NO.	
SPECIFIED				MASS												
				9				97.12.23	97.12.23	97.12.18	87.10.09	97.12.11	YAZAKI CORPORATION			