




PCB LAYOUT

SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)
5-6	5-4
(ON)=MOMENTARY	

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
- ▲ 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACTS: GOLD PLATED
5. TRAVEL: 1.0 mm
6. RATING: 0.4 VA max. @ 20V AC OR DC max.
7. CONTACT RESISTANCE: <100 MILLI-OHM
8. ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES.
9. INSULATION RESISTANCE: 500 MEGA-OHM min.
10. DIELECTRIC STRENGTH: 500 V RMS @SEA LEVEL.
11. OPERATING TEMP.: -30°C to 85°C
12. ▲ DENOTES CRITICAL PARAMETER.
13. SEAL RATING: IP67
14. 2002/95/EC (ROHS) COMPLIANT



E-SWITCH®

B	22253	UPDATED DRAWING TITLE	4/8/16	MJR
A	21940	New Release	8/3/2015	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 800USP8P1A1M2RE

SCALE 4:1

DATE 7/27/2015

DR rc

DWG T850000

REV B