




COIL: @ 25°C

RESISTANCE 850 OHMS $\pm 10\%$

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 7.0 VDC

MUST RELEASE 4.0 VDC MAX, 0.64 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX

RELEASE TIME 7.5 MS MAX

CONTACT STABILIZATION 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
1A 28 VDC RESISTIVE 100,000
OPERATIONS

DR. R.B. 11/21/97 CK ~~ERRY~~ 11/21/97

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. QPL

CUST. NO. M39016/16-043P

TYPE "JMCD" RELAY

JMSCD-12XPS